

Steckhülsen isoliert 6,3 mm Clips femelles à souder isolés Soldering receptacles insulated

DIN 46245/3

* ausgenommen
* excepté
* excepted

UL-No. E235796

mit Stützhülse

Werkstoff:
MS sn = Messing verzinkt

Temperaturbeständigkeit:
PVC -10°C bis +75°C
PA -55°C bis +105°C
HDPE -10°C bis +105°C
Schrumpftemperatur: 150°C

Strombelastbarkeit:
0.5 – 1.0 mm²/10A max.
1.5 – 2.5 mm²/15A max.
4.0 – 6.0 mm²/25A max.

avec douille-support

Matière:
MS sn = laiton étamé

Résistant à une température de:
PVC -10°C à +75°C
PA -55°C à +105°C
HDPE -10°C à +105°C
Température thermorétractable: 150°C


Intensité admissible:
0.5 – 1.0 mm²/10A max.
1.5 – 2.5 mm²/15A max.
4.0 – 6.0 mm²/25A max.




with extra support-sleeve


Material:
MS sn = tin-plated brass




Temperature range:
PVC -10°C up to +75°C
PA -55°C up to +105°C
HDPE -10°C up to +105°C
Shrink temperature: 150°C


Current carrying capacity:
0.5 – 1.0 mm²/10A max.
1.5 – 2.5 mm²/15A max.
4.0 – 6.0 mm²/25A max.






PVC									
mm ²	AWG	Grösse Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	DIN	L mm	A mm	øD mm	Werkzeuge Outils Toolings
0.5-1	22-18	6.3 x 0.8		3903	46245/T3	21	10.5	1.7	3974n,
1.5-2.5	16-14	6.3 x 0.8		3906	46245/T3	21	10.5	2.3	3983p.1, 3984c, 3984cx, 3984o, 3984ox, 3986c, 3986n, 3986s
4-6	12-10	6.3 x 0.8		3907	46245/T3	23.5	13	3.4	3974n, 3984o, 3986c, 3986n, 3986s



PVC									
mm ²	AWG	Grösse Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	DIN	L mm	øD mm	Werkzeuge Outils Toolings	
0.5-1	22-18	6.3 x 0.8		3944	*	21.5	1.7	3974n,	
1.5-2.5	16-14	6.3 x 0.8		3945	*	22	2.3	3983p.1, 3984c, 3984cx, 3984o, 3984ox, 3986c, 3986n, 3986s	
4-6	12-10	6.3 x 0.8		3947	*	24	3.4	3974n, 3984o, 3986c, 3986n, 3986s	



PA									
mm ²	AWG	Grösse Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	DIN	L mm	øD mm	Werkzeuge Outils Toolings	
0.5-1	22-18	6.3 x 0.8		3963	*	21	1.7	3974n,	
1.5-2.5	16-14	6.3 x 0.8		3966	*	22	2.3	3983p.1, 3984c, 3984cx, 3984o, 3984ox, 3986c, 3986n, 3986s	
4-6	12-10	6.3 x 0.8		3967	*	24	3.4	3974n, 3984o, 3986c, 3986n, 3986s	