

SIMATIC DP, CONNECTING MODULE FOR PROFINET
INTERFACE MODULES ET 200PRO; M12 / 7/8", 2 X M12 AND 2 X
7/8",



Figure similar

Input current	
from load voltage 2L+ (without load), max.	No current input, only infeed current, max. 8 A
from supply voltage 1L+, max.	No current input, only infeed current, max. 8 A
Interfaces	
PROFIBUS DP	
• Transmission rate, max.	100 Mbit/s; full-duplex, PROFINET
Accessories	
Function description	IM PN; 2xM12 2x7/8" interface module, power supply from 1L+ and 2L+ max. per 8 A, internal transfer 2L+ max. 8 A, 1L+ max. 5 A
belongs to product	M154-4PN High Feature
Weights	
Weight, approx.	540 g
last modified:	12.03.2015