



Nitrile

Long cuff version of the world's leading disposable glove for chemical splash protection, offering an unparalleled combination of chemical splash protection, comfort and durability

- Made with TNT Chemical Splash Resistance Technology for superior protection against harmful chemical splashes
- Super soft nitrile provides a comfortable, silky feel for extended wear
- Extended cuff for expanded protection over the wrist and forearm
- Silicone-free design is paint and finish process friendly



Industries

- Life Sciences
- Food Processing
- Automotive
- Machinery and Equipment
- Chemical

Recommended For

- Sample taking and processing
- Laboratory analysis
- Transferring liquids and solids
- Meat, Fish and Food Processing
- Industrial Production
- Maintenance
- Chemical Handling



TECHNICAL DATA SHEET

Product Information	
External Glove Surface	Textured Fingers
Audit Standards	ISO 9001
Packaging Overview	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Thailand
Product Segmentation	High Risk
Antistatic	Yes
Vulcanization Chemical Accelerators	<ul style="list-style-type: none"> Zinc Dibutyldithiocarbamate (ZDBC) <p><i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i></p>

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	300 / 12		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.12/4.7		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.16/6.3		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 6	≥ 6	EN 455-2

ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	92605070	92605080	92605090	92605100

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Technology



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

