

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2064611200](#)  
**Status:** **Active**  
**Overview:** [Micro-Fit Connector System](#)  
**Description:** [Micro-Fit+ Receptacle Housing, Dual Row, 12 Circuits, UL 94V-0, Black](#)

**Documents:**

[Drawing \(PDF\)](#) [Test Summary 2064600000-TS-000 \(PDF\)](#)  
[Product Specification 2064600000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification 2064610000-PK-000 \(PDF\)](#)

**Agency Certification**

UL E29179

**General**

Product Family Crimp Housings  
 Series [206461](#)  
 Application Power, Wire-to-Board  
 Datasheet Order No 987651-9552  
 Overview [Micro-Fit Connector System](#)  
 Product Name Micro-Fit+  
 UPC 191130004058


**Physical**

Circuits (maximum) 12  
 Color - Resin Black  
 Flammability 94V-0  
 Gender Receptacle  
 Glow-Wire Capable Yes  
 Keying to Mating Part None  
 Lock to Mating Part Yes  
 Material - Resin Nylon  
 Net Weight 1.263/g  
 Number of Rows 2  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface 3.00mm  
 Polarized to Mating Part Yes  
 Temperature Range - Operating -40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification 2064610000-PK-000  
 Product Specification 2064600000-PS-000  
 Sales Drawing 2064610000-SD-000  
 Test Summary 2064600000-TS-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/88/2018 (15  
 January 2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[206461](#) Series

**Mates With**

Micro-Fit+ Header [206832](#)

**Use With**

Micro-Fit+ Female Terminal [206460](#)