



DATE	REV	DESCRIPTION	BY	CHKD



equip CAT.6A SSTP 10 GIGABIT ETHERNET
 PATCH CABLE ISO/IEC 11801 & EN 50288 &
 TIA/EIA-568-B.2 & IEC 332.1 26AWGX4P LSOH



PA/R	PINOUT		
	P1 (T568B)	WIRE	P2 (T568B)
1	1	WHT/ORG	1
	2	ORG	2
2	3	WHT/GRN	3
	6	GRN	6
3	4	BLU	4
	5	WHT/BLU	5
4	7	WHT/BRN	7
	8	BRN	8


Conductor	Bare Copper 26AWG 7/0.16±0.005mm
Insulation	Thickness:MIN at any point:0.265mm MAX AVG:0.296mm Diameter:1.07±0.03mm
Jacketing LSOH	Thickness:MIN at any point:0.40mm MAX AVG:0.45mm Diameter:6.1±0.3mm


Wire	CAT. 6A PIMF STR 26AWG *4P
Plug	8P8C, 50µ gold plating
Length	0.5m, 1m, 2m, 3m, 5m, 10m, 15m, 20m
Length printing on each plug	

color/length index		
length	color	item no.
0,50 m	color x	6056x7
1,00 m	color x	6056x0
2,00 m	color x	6056x1
3,00 m	color x	6056x2
5,00 m	color x	6056x4
10,00 m	color x	6056x6
15,00 m	color x	6056x8
20,00 m	color x	6056x9
1,00 m	blue	605830
1,00 m	green	605840
white (x=1), red (x=2), blue (x=3), green (x=4), yellow (x=6), orange (x=7), black (x=9)		



Unless specified on the drawing, tolerances are per the follows:
 .X ± 1
 .X ± 0.2
 .XX ± 0.05





Patch Cable Cat. 6A SSTP (PIMF) 26 AWG,
LSOH

UNIT	MM	SHEET	1	OF	1
------	----	-------	---	----	---