




Have a Question?
Chat with a Product Information Specialist

What can we help you find?

962999-1 Product Details

[Share](#) [Print](#) [Email](#)



962999-1

TE Internal Number: 962999-1

Active

[View 3D PDF](#)

1.5/2.5/4.0mm Pin Diameter Connector System

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Contact
- Product Series = 1.5 mm System
- Contact Type = Socket
- CuNiSi Contact Base Material
- Tin Contact Plating, Mating Area, Material

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [DIA. 1.5 mm SOCKET CONTACT DIA.1.5 mm Buchsenkontakt](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version M5)
- [3D Model](#) (IGES, Version M5)
- [3D Model](#) (STEP, Version M5)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Contact
- [Product Series](#) = 1.5 mm System
- [Sealed](#) = Yes

Body Features:

- [Wire Range \(mm \[AWG\]\)](#) = 1.00-2.50² [17-13]
- Single Seal Part No. = 828905-1

Contact Features:

- Contact Type = Socket
- Contact Base Material = CuNiSi
- [Contact Plating, Mating Area, Material](#) = Tin

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Accepts Wire Insulation Diameter, Range \(mm \[in\]\)](#) = 2.21 - 3.00 [0.087 - 0.118]

Packaging Features:

- [Packaging Method](#) = Loose Piece
- Packaging Quantity = 500/Box

Other:

- GET 0.64 Connector System = No
- Brand = AMP

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)