

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5601230800](#)
Status: **Active**
Overview: [DuraClik™ Connector System](#)
Description: [DuraClik™ ISL Wire-to-Board Receptacle Housing, Single Row, White, 8 Circuits](#)

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General

Product Family	Crimp Housings
Series	560123
Application	Signal, Wire-to-Board
Overview	DuraClik™ Connector System
Product Name	DuraClik™
UPC	889056009553

Physical

Circuits (maximum)	8
Color - Resin	White
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	0.455/g
Number of Rows	1
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Ports	8
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	3.0A
-------------------------------	------


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-560123-005
---------------	---------------



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Not Relevant

Compliant

Search Parts in this Series

[560123](#) Series

Mates With

[502352](#) Right-Angle DuraClik™ Wire-to-Board Header, [560020](#) Vertical DuraClik™ Wire-to-Board Header

Use With

[560124](#) DuraClik™ ISL Terminal
[560125](#) DuraClik™ ISL Retainer