


Part Number: 1905X36X

Type	Size	Rating	Description
LED	M8	24Vac	LED Recessed Panel Indicator

Dimensions (mm)



Part #	Colour	Current (mA)	Intensity (mcd @ 12Vdc)
1905X360	Red	13	6
1905X363	Bright Red	13	32
1905X361	Green	13	26
1905X362	Yellow	13	26
1905X367	Blue	10	45

Bezel types - X=0 satin chrome / X=1 black chrome / X=2 matt chrome

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Luminous intensity at DC
- 3 Storage temperature -25 °C to +80°C
- 4 Application temperature -20 °C to +60°C
- 5 Due to component tolerances, colour temperature variations may be observed
- 6 The terminals are not qualified for soldering
- 7 Sealed to IP67 above panel when supplied gasket used
- 8 The plastic(polycarbonate) has limited chemical resistance
- 9 RoHS & REACH SVHC compliant