

Die, HSS MF right, pre-slotted and 1.75 thread chamfer

for universal use up to 700 N/mm²

ORION[®]

Application:

For cutting fine metric threads externally in the material groups of steel and non-ferrous metals up to a strength of 700 N/mm².

Execution:

- right die, tol. 6 g with spiral point, pre-slotted and 1.75 pitch

Advantage:

- standard geometry with excellent price/performance ratio

| | |
|---------------------------------------|--------------------|
| Art. no. | 13445 086 |
| Brand | ORION |
| Manufacturer Part Number | 13445086 |
| Thread type | Metric fine thread |
| Cutting material | HSS |
| Tolerance of dies | 6 g |
| Thread type x nominal diameter | MF8 |
| Pitch | 1 mm |
| Outer diameter | 25 mm |
| Height | 9 mm |
| Cutting direction | Right-hand cutting |
| Gross Weight | 0.025 kg |
| Product Group | 1DC |



EAN

4039247073573