

Die, HSSE G right, nitrided, pre-slotted and 2.0 thread chamfer

For universal use up to 1300 N/mm²

ORION[®]

Application:

For tapping male (pipe) threads in the steel, stainless steel, NF metal and special alloy material groups up to a strength of 1300 N/mm².

Execution:

- Right-handed die, tol. A with spiral point, pre-slotted, 2.0-threaded chamfer

Advantage:

- Standard geometry with a very good price-performance ratio



Art. no.	13488 010
Brand	ORION
Manufacturer Part Number	13488010
Thread type	Pipe thread
Cutting material	HSSE
Tolerance of dies	A
Thread type x nominal diameter in inches	G 1/8 in
Number of thread starts per inch	28
Outer diameter	30 mm
Height	11 mm
Cutting direction	Right-hand cutting
Gross Weight	0.045 kg
Product Group	1DC

EAN

4039247074822