

## Reducing sleeves E1 + E2 with slot

With groove

**ORION**<sup>®</sup>

### Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm<sup>2</sup>
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground



|                                 |                  |
|---------------------------------|------------------|
| <b>Art. no.</b>                 | <b>22778 237</b> |
| <b>Brand</b>                    | ORION            |
| <b>Manufacturer Part Number</b> | 22778237         |
| <b>Clamping diameter</b>        | 40 mm            |
| <b>Clamping diameter 2</b>      | 32 mm            |
| <b>Collar diameter</b>          | 45 mm            |
| <b>Length</b>                   | 69 mm            |
| <b>Collar width</b>             | 3 mm             |
| <b>Clearance</b>                | 5 mm             |
| <b>Length 2</b>                 | 61 mm            |
| <b>Groove width</b>             | 17 mm            |
| <b>Gross Weight</b>             | 0.650 kg         |
| <b>Product Group</b>            | 2AL              |

### EAN

4053625466153