

## All-steel screw clamps 120–600 mm clamping width

With slip and spindle lock, 2-C handle

**ATORN**<sup>®</sup>

### Application

For sprung and elastic clamping of a range of workpieces.

### Version

- Fixed clamp made of cold-drawn profile steel, hardened and galvanised
- Sliding clamp drop-forged, hardened and galvanised
- Movable pressure plate with integrated spindle safety device
- Smooth running, burnished steel spindle with trapezoidal thread

### Advantage

- Ergonomic two-component handle for optimum force transmission

<b>Art. no.</b>	<b>51105 040</b>
<b>Max. clamping width</b>	400 mm
<b>Overhang</b>	120 mm
<b>Rail cross-section L x W</b>	12 x 25 mm
<b>Material of the grip handle</b>	2-component plastic



### EAN-Code

4050293648102