

GB 18 LTX BL Q I cordless screw tap

Full-fledged cordless drill screwdriver with unique, patented thread cutting function

metabo

Version:

- With two quick-change screw tap chucks for accommodating screw taps with square and cylindrical drill bits
- Metabo Quick system: Fast changing of tool chuck and plug-in tool for flexible working
- Impulse mode function for unscrewing seized screws and spot-drilling on smooth surfaces
- Precision Stop: electronic torque coupling with increased precision for accurate and sensitive work
- Overload protection: protects the motor from overheating

Advantage:

- Fast and interruption-free drilling and cleaning of threads by automatic switching of the direction of rotation
- The screw taps have long service life thanks to intelligent torque monitoring
- Electronic safety cut-off: no kick-back if the drill jams – for excellent user protection

Delivery:

2 x battery 18 V/5.2Ah, charger ASC 55, in metaBOX incl. quick-change screw tap chuck M4-M6 and M8-M12, additional handle, belt hook and bit depot



Art. no.	71037 897
Model	GB 18 LTX Q I
Motor design	Brushless motor
Number of rechargeable batteries/batteries	2 PCS
Type of rechargeable battery/battery	Li-Ion
Battery voltage	18 V
Rechargeable battery/battery capacity	5.2 Ah
Max. drilling diameter in wood	65 mm
Max. drilling diameter in steel	13 mm
Max. thread-cutting performance	M12
Min. thread-cutting performance	M4
Idle speed 1st gear min./max.	0-500 rpm
Max. torque hard/soft	130 / 65 Nm
Idle speed 2nd gear min./max.	0-2000 rpm
Min./max. drill chuck span width	1.5-13 mm
Battery included	Yes
With working lights	No
With rubber-coated handle	Yes
With quick clamping system	Yes
With overload protection	Yes
With impulse function	Yes
With battery capacity display	Yes
Tool holding device	Metabo Quick
Min./max. torque adjustment	1-20 Nm

EAN-Code

4061792188105