

CAT6A S/FTP Ultraflex Patch Cable

Technical Features

Cat.6A RJ45 shielded plugs with Cat.7 S/FTP raw cable

Flexible and soft cable (min. bending radius: 25 mm)

10 Gigabit Ethernet, PoE, PoE+, PoE++

Cat.6A ISO11801 Channel Class EA

EN50173 & ANSI/TIA 568C.2

4x2xAWG26/7 bare copper wire


Low smoke (IEC 61034)

Halogen free (IEC 60754-2)

Flame retardant (IEC 60332-1-2)

Operating temperature: -20°C–75°C

Technical Drawing



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Art-No.	Cable Length	Color	EAN Code
C6A011S	0.25 m	White	4052792055634
C6A021S	0.5 m	White	4052792055641
C6A031S	1 m	White	4052792055658
C6A041S	1.5 m	White	4052792055656
C6A051S	2 m	White	4052792055672
C6A061S	3 m	White	4052792055689
C6A071S	5 m	White	4052792055696
C6A081S	7.5 m	White	4052792055702
C6A091S	10 m	White	4052792055719
C6A101S	15 m	White	4052792055726
C6A111S	20 m	White	4052792055733
C6A121S	30 m	White	4052792055740
C6A141S	50 m	White	4052792055757

Art-No.	Cable Length	Color	EAN Code
C6A012S	0.25 m	Grey	4052792055764
C6A022S	0.5 m	Grey	4052792055771
C6A032S	1 m	Grey	4052792055788
C6A042S	1.5 m	Grey	4052792055795
C6A052S	2 m	Grey	4052792055801
C6A062S	3 m	Grey	4052792055818
C6A072S	5 m	Grey	4052792055825
C6A082S	7.5 m	Grey	4052792055832
C6A092S	10 m	Grey	4052792055849
C6A102S	15 m	Grey	4052792055856
C6A112S	20 m	Grey	4052792055863
C6A122S	30 m	Grey	4052792055870
C6A142S	50 m	Grey	4052792055887

Art-No.	Cable Length	Color	EAN Code
C6A013S	0.25 m	Black	4052792055894
C6A023S	0.5 m	Black	4052792055900
C6A033S	1 m	Black	4052792055917
C6A043S	1.5 m	Black	4052792055924
C6A053S	2 m	Black	4052792055931
C6A063S	3 m	Black	4052792055948
C6A073S	5 m	Black	4052792055955
C6A083S	7.5 m	Black	4052792055962
C6A093S	10 m	Black	4052792055979
C6A103S	15 m	Black	4052792055986
C6A113S	20 m	Black	4052792055993
C6A123S	30 m	Black	4052792056006
C6A143S	50 m	Black	4052792056013

Art-No.	Cable Length	Color	EAN Code
C6A014S	0.25 m	Red	4052792056020
C6A024S	0.5 m	Red	4052792056037
C6A034S	1 m	Red	4052792056044
C6A044S	1.5 m	Red	4052792056051
C6A054S	2 m	Red	4052792056068
C6A064S	3 m	Red	4052792056075
C6A074S	5 m	Red	4052792056082
C6A084S	7.5 m	Red	4052792056099
C6A094S	10 m	Red	4052792056105
C6A104S	15 m	Red	4052792056112
C6A114S	20 m	Red	4052792056129

Art-No.	Cable Length	Color	EAN Code
C6A015S	0.25 m	Green	4052792056136
C6A025S	0.5 m	Green	4052792056143
C6A035S	1 m	Green	4052792056150
C6A045S	1.5 m	Green	4052792056167
C6A055S	2 m	Green	4052792056174
C6A065S	3 m	Green	4052792056181
C6A075S	5 m	Green	4052792056198
C6A085S	7.5 m	Green	4052792056204
C6A095S	10 m	Green	4052792056211
C6A105S	15 m	Green	4052792056228
C6A115S	20 m	Green	4052792056235


Art-No.	Cable Length	Color	EAN Code
C6A016S	0.25 m	Blue	4052792056242
C6A026S	0.5 m	Blue	4052792056259
C6A036S	1 m	Blue	4052792056266
C6A046S	1.5 m	Blue	4052792056273
C6A056S	2 m	Blue	4052792056280
C6A066S	3 m	Blue	4052792056297
C6A076S	5 m	Blue	4052792056303
C6A086S	7.5 m	Blue	4052792056310
C6A096S	10 m	Blue	4052792056327
C6A106S	15 m	Blue	4052792056334
C6A116S	20 m	Blue	4052792056341

Art-No.	Cable Length	Color	EAN Code
C6A017S	0.25 m	Yellow	4052792056358
C6A027S	0.5 m	Yellow	4052792056365
C6A037S	1 m	Yellow	4052792056372
C6A047S	1.5 m	Yellow	4052792056389
C6A057S	2 m	Yellow	4052792056396
C6A067S	3 m	Yellow	4052792056402
C6A077S	5 m	Yellow	4052792056419
C6A087S	7.5 m	Yellow	4052792056426
C6A097S	10 m	Yellow	4052792056433
C6A107S	15 m	Yellow	4052792056440
C6A117S	20 m	Yellow	4052792056457

Art-No.	Cable Length	Color	EAN Code
C6A019S	0.25 m	Purple	4052792056570
C6A029S	0.5 m	Purple	4052792056587
C6A039S	1 m	Purple	4052792056594
C6A049S	1.5 m	Purple	4052792056600
C6A059S	2 m	Purple	4052792056617
C6A069S	3 m	Purple	4052792056624
C6A079S	5 m	Purple	4052792056631
C6A089S	7.5 m	Purple	4052792056648
C6A099S	10 m	Purple	4052792056655
C6A109S	15 m	Purple	4052792056662
C6A119S	20 m	Purple	4052792056679

Package Content

1x CAT6A S/FTP Ultraflex Patch Cable



Packaging Information

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
C6A011S	360x80x6 mm	0,018 kg	400x300x280 mm	450 pcs	8,6 kg
C6A021S	140x180x20 mm	0,025 kg	400x300x280 mm	260 pcs	7,1 kg
C6A031S	140x180x20 mm	0,041 kg	400x300x280 mm	180 pcs	7,9 kg
C6A041S	150x200x25 mm	0,057 kg	400x300x280 mm	120 pcs	7,4 kg
C6A051S	150x200x25 mm	0,072 kg	400x300x280 mm	100 pcs	7,8 kg
C6A061S	200x250x30 mm	0,103 kg	400x300x280 mm	80 pcs	8,8 kg
C6A071S	200x250x30 mm	0,164 kg	400x300x280 mm	50 pcs	8,8 kg
C6A081S	200x250x50 mm	0,24 kg	400x300x280 mm	35 pcs	9 kg
C6A091S	200x250x50 mm	0,313 kg	400x300x280 mm	30 pcs	10 kg
C6A101S	250x300x50 mm	0,34 kg	400x300x280 mm	20 pcs	7,4 kg
C6A111S	250x300x65 mm	0,628 kg	400x300x280 mm	18 pcs	11,9 kg
C6A121S	300x350x70 mm	0,914 kg	400x300x280 mm	14 pcs	13,4 kg
C6A141S	300x350x80 mm	1,55 kg	400x300x280 mm	8 pcs	13 kg

Packaging Information

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
C6A012S	360x80x6 mm	0,018 kg	400x300x280 mm	450 pcs	8,6 kg
C6A022S	140x180x20 mm	0,025 kg	400x300x280 mm	260 pcs	7 kg
C6A032S	140x180x20 mm	0,041 kg	400x300x280 mm	180 pcs	7,9 kg
C6A042S	150x200x25 mm	0,057 kg	400x300x280 mm	120 pcs	7,4 kg
C6A052S	150x200x25 mm	0,072 kg	400x300x280 mm	100 pcs	7,8 kg
C6A062S	200x250x30 mm	0,103 kg	400x300x280 mm	80 pcs	8,8 kg
C6A072S	200x250x30 mm	0,164 kg	400x300x280 mm	50 pcs	8,8 kg
C6A082S	200x250x50 mm	0,24 kg	400x300x280 mm	35 pcs	9 kg
C6A092S	200x250x50 mm	0,313 kg	400x300x280 mm	30 pcs	10 kg
C6A102S	250x300x50 mm	0,34 kg	400x300x280 mm	20 pcs	7,4 kg
C6A112S	250x300x65 mm	0,628 kg	400x300x280 mm	18 pcs	11,9 kg
C6A122S	300x350x70 mm	0,914 kg	400x300x280 mm	14 pcs	13,4 kg
C6A142S	300x350x80 mm	1,55 kg	400x300x280 mm	8 pcs	13 kg

Packaging Information

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
C6A013S	360x80x6 mm	0,018 kg	400x300x280 mm	450 pcs	8,6 kg
C6A023S	140x180x20 mm	0,025 kg	400x300x280 mm	260 pcs	7,1 kg
C6A033S	140x180x20 mm	0,041 kg	400x300x280 mm	180 pcs	7,9 kg
C6A043S	150x200x25 mm	0,057 kg	400x300x280 mm	120 pcs	7,4 kg
C6A053S	150x200x25 mm	0,072 kg	400x300x280 mm	100 pcs	7,8 kg
C6A063S	200x250x30 mm	0,103 kg	400x300x280 mm	80 pcs	8,8 kg
C6A073S	200x250x30 mm	0,164 kg	400x300x280 mm	50 pcs	8,8 kg
C6A083S	200x250x50 mm	0,24 kg	400x300x280 mm	35 pcs	9 kg
C6A093S	200x250x50 mm	0,313 kg	400x300x280 mm	30 pcs	10 kg
C6A103S	250x300x50 mm	0,34 kg	400x300x280 mm	20 pcs	7,4 kg
C6A113S	250x300x65 mm	0,628 kg	400x300x280 mm	18 pcs	11,9 kg
C6A123S	300x350x70 mm	0,914 kg	400x300x280 mm	14 pcs	13,4 kg
C6A143S	300x350x80 mm	1,55 kg	400x300x280 mm	8 pcs	13 kg

Packaging Information

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
C6A014S	360x80x6 mm	0,018 kg	400x300x280 mm	450 pcs	8,6 kg
C6A024S	140x180x20 mm	0,025 kg	400x300x280 mm	260 pcs	7,1 kg
C6A034S	140x180x20 mm	0,041 kg	400x300x280 mm	180 pcs	7,9 kg
C6A044S	150x200x25 mm	0,057 kg	400x300x280 mm	120 pcs	7,4 kg
C6A054S	150x200x25 mm	0,072 kg	400x300x280 mm	100 pcs	7,8 kg
C6A064S	200x250x30 mm	0,103 kg	400x300x280 mm	80 pcs	8,8 kg
C6A074S	200x250x30 mm	0,164 kg	400x300x280 mm	50 pcs	8,8 kg
C6A084S	200x250x50 mm	0,24 kg	400x300x280 mm	35 pcs	9 kg
C6A094S	200x250x50 mm	0,313 kg	400x300x280 mm	30 pcs	10 kg
C6A104S	250x300x50 mm	0,34 kg	400x300x280 mm	20 pcs	7,4 kg
C6A114S	250x300x65 mm	0,628 kg	400x300x280 mm	18 pcs	11,9 kg

Packaging Information

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
C6A015S	360x80x6 mm	0,018 kg	400x300x280 mm	450 pcs	8,6 kg
C6A025S	140x180x20 mm	0,025 kg	400x300x280 mm	260 pcs	7,1 kg
C6A035S	140x180x20 mm	0,041 kg	400x300x280 mm	180 pcs	7,9 kg
C6A045S	150x200x25 mm	0,057 kg	400x300x280 mm	120 pcs	7,4 kg
C6A055S	150x200x25 mm	0,072 kg	400x300x280 mm	100 pcs	7,8 kg
C6A065S	200x250x30 mm	0,103 kg	400x300x280 mm	80 pcs	8,8 kg
C6A075S	200x250x30 mm	0,164 kg	400x300x280 mm	50 pcs	8,8 kg
C6A085S	200x250x50 mm	0,24 kg	400x300x280 mm	35 pcs	9 kg
C6A095S	200x250x50 mm	0,313 kg	400x300x280 mm	30 pcs	10 kg
C6A105S	250x300x50 mm	0,34 kg	400x300x280 mm	20 pcs	7,4 kg
C6A115S	250x300x65 mm	0,628 kg	400x300x280 mm	18 pcs	11,9 kg

Packaging Information

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
C6A016S	360x80x6 mm	0,018 kg	400x300x280 mm	450 pcs	8,6 kg
C6A026S	140x180x20 mm	0,025 kg	400x300x280 mm	260 pcs	7,1 kg
C6A036S	140x180x20 mm	0,041 kg	400x300x280 mm	180 pcs	7,9 kg
C6A046S	150x200x25 mm	0,057 kg	400x300x280 mm	120 pcs	7,4 kg
C6A056S	150x200x25 mm	0,072 kg	400x300x280 mm	100 pcs	7,8 kg
C6A066S	200x250x30 mm	0,103 kg	400x300x280 mm	80 pcs	8,8 kg
C6A076S	200x250x30 mm	0,164 kg	400x300x280 mm	50 pcs	8,8 kg
C6A086S	200x250x50 mm	0,24 kg	400x300x280 mm	35 pcs	9 kg
C6A096S	200x250x50 mm	0,313 kg	400x300x280 mm	30 pcs	10 kg
C6A106S	250x300x50 mm	0,34 kg	400x300x280 mm	20 pcs	7,4 kg
C6A116S	250x300x65 mm	0,628 kg	400x300x280 mm	18 pcs	11,9 kg

Packaging Information

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
C6A017S	360x80x6 mm	0,018 kg	400x300x280 mm	450 pcs	8,6 kg
C6A027S	140x180x20 mm	0,025 kg	400x300x280 mm	260 pcs	7,1 kg
C6A037S	140x180x20 mm	0,041 kg	400x300x280 mm	180 pcs	7,9 kg
C6A047S	150x200x25 mm	0,057 kg	400x300x280 mm	120 pcs	7,4 kg
C6A057S	150x200x25 mm	0,072 kg	400x300x280 mm	100 pcs	7,8 kg
C6A067S	200x250x30 mm	0,103 kg	400x300x280 mm	80 pcs	8,8 kg
C6A077S	200x250x30 mm	0,164 kg	400x300x280 mm	50 pcs	8,8 kg
C6A087S	200x250x50 mm	0,24 kg	400x300x280 mm	35 pcs	9 kg
C6A097S	200x250x50 mm	0,313 kg	400x300x280 mm	30 pcs	10 kg
C6A107S	250x300x50 mm	0,34 kg	400x300x280 mm	20 pcs	7,4 kg
C6A117S	250x300x65 mm	0,628 kg	400x300x280 mm	18 pcs	11,9 kg

Packaging Information

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
C6A019S	360x80x6 mm	0,018 kg	400x300x280 mm	450 pcs	8,6 kg
C6A029S	140x180x20 mm	0,025 kg	400x300x280 mm	260 pcs	7,1 kg
C6A039S	140x180x20 mm	0,041 kg	400x300x280 mm	180 pcs	7,9 kg
C6A049S	150x200x25 mm	0,057 kg	400x300x280 mm	120 pcs	7,4 kg
C6A059S	150x200x25 mm	0,072 kg	400x300x280 mm	100 pcs	7,8 kg
C6A069S	200x250x30 mm	0,103 kg	400x300x280 mm	80 pcs	8,8 kg
C6A079S	200x250x30 mm	0,164 kg	400x300x280 mm	50 pcs	8,8 kg
C6A089S	200x250x50 mm	0,24 kg	400x300x280 mm	35 pcs	9 kg
C6A099S	200x250x50 mm	0,313 kg	400x300x280 mm	30 pcs	10 kg
C6A109S	250x300x50 mm	0,34 kg	400x300x280 mm	20 pcs	7,4 kg
C6A119S	250x300x65 mm	0,628 kg	400x300x280 mm	18 pcs	11,9 kg