

## NOXLITE LED HP FLOODLIGHT II

Outdoor LED flood- and spotlights



### Areas of application

- Driveways
- Garages
- Yards
- Pathway lighting
- Outdoor use (only roofed areas)

### Product benefits

- Quick installation
- Easy change of housing, even between two different wattages

### Product features

- Efficient LED floodlight with high light output
- Lighting panel can be swivelled round
- Sensor function can be turned off via switch (manual luminaire switch-off required)
- Available in two housing colors
- Color temperature: 3,000 K
- Color rendering index  $R_a$ : > 80
- Type of protection: IP44
- Protection class: I
- Lifetime (L70/B50): up to 35,000 h



# Product family datasheet


## Technical data

Product description	Electrical data			Photometrical data				Dimensions & weight			Colors & materials
	Nominal wattage	Nominal voltage	Mains frequency	Color temperature	Luminous flux	Light color (designation)	Color rendering index Ra	Length	Width	Height	Body material
NOXLITE LED HP FLOODLIGHT 23 W WT	22 W	220...240 V	50/60 Hz	3000 K	1470 lm	Warm white	>80	189.0 mm	167.0 mm	203.0 mm	Aluminum
NOXLITE LED HP FLOODLIGHT 40 W WT	40 W	220...240 V	50/60 Hz	3000 K	3000 lm	Warm white	>80	211.0 mm	171.0 mm	229.0 mm	Aluminum
NOXLITE LED HP FLOODLIGHT 23 W GR	22 W	220...240 V	50/60 Hz	3000 K	1470 lm	Warm white	>80	189.0 mm	167.0 mm	203.0 mm	Aluminum
NOXLITE LED HP FLOODLIGHT 40 W GR	40 W	220...240 V	50/60 Hz	3000 K	3000 lm	Warm white	>80	211.0 mm	171.0 mm	229.0 mm	Aluminum


Product description	Product color	Cover material	Temperatures & operating conditions	Additional product data	Capabilities		
			Ambient temperature range	Equipped with lamp	Type of installation	Type of connection	Accessories
NOXLITE LED HP FLOODLIGHT 23 W WT	White	Polykarbonát (PC), UV stabilizace	-20...+40 °C	Yes	Direct mounting/Surface-mounted	Terminal, 3-pole	Screw / Dovels / Washers
NOXLITE LED HP FLOODLIGHT 40 W WT	White	Polykarbonát (PC), UV stabilizace	-20...+40 °C	Yes	Direct mounting/Surface-mounted	Terminal, 3-pole	Screw / Dovels / Washers
NOXLITE LED HP FLOODLIGHT 23 W GR	Anthracite	Polykarbonát (PC), UV stabilizace	-20...+40 °C	Yes	Direct mounting/Surface-mounted	Terminal, 3-pole	Screw / Dovels / Washers
NOXLITE LED HP FLOODLIGHT 40 W GR	Anthracite	Polykarbonát (PC), UV stabilizace	-20...+40 °C	Yes	Direct mounting/Surface-mounted	Terminal, 3-pole	Screw / Dovels / Washers

## Product family datasheet


	Certificates & standards		Country specific categorizations
Product description	Protection class	Type of protection	Order reference
NOXLITE LED HP FLOODLIGHT 23 W WT	I	IP44	NXL LED HPFLOOD
NOXLITE LED HP FLOODLIGHT 40 W WT	I	IP44	NXL LED HPFLOOD
NOXLITE LED HP FLOODLIGHT 23 W GR	I	IP44	NXL LED HPFLOOD
NOXLITE LED HP FLOODLIGHT 40 W GR	I	IP44	NXL LED HPFLOOD




NOXLITE LED HP FLOODLIGHT 23 W  
WT, NOXLITE LED HP FLOODLIGHT 23  
W GR



NOXLITE LED HP FLOODLIGHT 40 W  
WT, NOXLITE LED HP FLOODLIGHT 40  
W GR



NOXLITE LED HP FLOODLIGHT 23 W  
WT, NOXLITE LED HP FLOODLIGHT 23  
W GR



NOXLITE LED HP FLOODLIGHT 40 W  
WT, NOXLITE LED HP FLOODLIGHT 40  
W GR

## Product family datasheet

---

### Application advice

For more detailed application information and graphics please see product datasheet.

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899917996	NOXLITE LED HP FLOODLIGHT 23 W WT	Shipping carton box 2	408 mm x 227 mm x 333 mm	30.84 dm <sup>3</sup>	3506.00 g
4052899918009	NOXLITE LED HP FLOODLIGHT 40 W WT	Shipping carton box 2	408 mm x 248 mm x 350 mm	35.41 dm <sup>3</sup>	4638.00 g
4052899905603	NOXLITE LED HP FLOODLIGHT 23 W GR	Shipping carton box 2	408 mm x 227 mm x 333 mm	30.84 dm <sup>3</sup>	3524.00 g
4052899905610	NOXLITE LED HP FLOODLIGHT 40 W GR	Shipping carton box 2	408 mm x 248 mm x 350 mm	35.41 dm <sup>3</sup>	4568.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.