






# Subracks - europac PRO ServicePLUS

## Side panels type L

### Order Information

Height U		Depth mm	Side panel type L   06197002 Al, 2 mm, passivated	Front cover   BZA45810 for decorative finish of 19" bracket, Al, 2 mm, anodised	Collar screw with slot for assembly of front cover   06708055 M6 x 16, St, nickel-plated	Sleeves for assembly of front cover   00508056 PPE, black	Side panel connection   BPA45867 Zn die-cast, incl. fixing material kit, for connecting two by two side panels (on top of each other)
			1 piece		PU 100 pieces	PU 100 pieces	PU 4 pieces
3		175	<b>34561-185</b>				
3		235	<b>34561-187</b>				
3		275 1)	-				
3		277.75 2)	-	<b>34561-197</b>	<b>21100-565</b>	<b>21100-566</b>	<b>21101-954</b>
3		295	<b>34561-189</b>				
3		355	-				
3		415	-				
3		475	-				
4		175 3)					
4		235 3)					
4		295 3)	-				
4		355 3)					
4		415 3)					
4		475 3)					
6		175	<b>34561-485</b>				
6		235	<b>34561-487</b>				
6		275 1)	-				
6		277.75 2)	-	<b>34561-497</b>	<b>21100-565</b>	<b>21100-566</b>	<b>21101-954</b>
6		295	<b>34561-489</b>				
6		355	-				
6		415	-				
6		475	-				
6		970	-				
9		175					
9		235					
9		295	-				
9		355					
9		415					
			Screw, M4 x 14, PU 100 pieces, for fastening horizontal rail to side panel	<b>24560-130</b>	-	-	-
			Screw, M4 x 10, required if guide rails are screwed to slot 1, PU 100 pieces	<b>24560-155</b>	-	-	-

1) CompactPCI 2) VME64x 3) Grid holes of side panel 3 + 1 U