

Frame type plug-in units PRO with hood

Plug-in units PRO with hood, 3/6 U, front panel unshielded



Illustration shows 12 HP width, side panel depth 167 mm

04808002

- Protects a PCB against mechanical damage and deflects electrostatic discharge; for euroboard formats
- Suitable in all subracks and these cases: ratiopacPRO/-air, propacPRO and compacPRO
- Useable connectors in accordance with EN 60603-2 (DIN 41612)
- 2 depths, for 160 mm or 220 mm board

Delivery comprises (kit)

Item	Qty	Description
1	1	Front panel, Al, 2.5 mm, anodised, cut edges plain
2	1	Handle, grey, PPE, UL 94 V-1
3	1	Side panel, Al extrusion, colourless passivated, with groove for one PCB
4	1	Hood, Al, 1 mm, with perforation, rear panel integrated
5	1	Assembly kit (incl. PCB fixing for slot 1)



ServicePLUS see page 7.74

Order Information

Height U	Width HP	Depth = 167 mm		Depth = 227 mm	
		Part no.	Part no.	Part no.	Part no.
3	5	24812-005	24812-055		
3	6	24812-006	24812-056		
3	7	24812-007	24812-057		
3	10	24812-010	24812-060		
3	12	24812-012	24812-062		
3	14	24812-014	24812-064		
6	5	24812-505	24812-555		
6	6	24812-506	24812-556		
6	7	24812-507	24812-557		
6	10	24812-510	24812-560		
6	12	24812-512	24812-562		
6	14	24812-514	24812-564		

■ Dimension drawings see from page 7.88