

## Nr. 220 Loose Roller Bearings with Round Groove

made of cast iron, in heavier, robust execution, with roller cage, bolts and two nuts.  
All dimensions in mm.



Außen-Ø	50	60	75	90	105	120
Rillengrund-Ø	38	46	59	72	85	100
Rillenbreite	9	9	9	9	11	11
Rillentiefe	6	7	8	9	10	10
Kranzbreite	18	18	19	20	22	22
Bohrung für Bolzen	12	12	12	12	12	12
Nabenlänge	27	27	27	27	32	32
Naben-Ø	34	34	34	34	36	36
Achslänge	62	62	62	62	70	70
Seil-Ø max.	8	8	8	8	10	10
Tragfähigkeit in kg	30	30	40	50	75	100
Gewicht in kg ca.	0,30	0,36	0,40	0,55	0,75	1,00

Außen-Ø	140	160	180	200	225	250
Rillengrund-Ø	120	140	160	180	195	220
Rillenbreite	14	14	14	14	16	16
Rillentiefe	10	10	10	10	15	15
Kranzbreite	27	27	28	28	38	38
Bohrung für Bolzen	16	16	16	16	22	22
Nabenlänge	34	34	34	34	50	50
Naben-Ø	48	48	51	51	70	70
Achslänge	85	85	85	85	125	125
Seil-Ø max.	13	13	13	13	15	15
Tragfähigkeit in kg	150	175	200	200	250	250
Gewicht in kg ca.	1,60	1,80	2,50	2,90	5,20	7,00