

M50 Polyamide (PA) Gland Light Grey (30-38mm)



Basic data:

ID	0004410012
GTIN	7630268414993



Features:

Nylon cable gland M50 with lock nut light grey

Technical data:

Thread type:	Metric
Nominal thread size metric/PG:	50
Pitch thread:	1.5 mm
Thread length:	18 mm
Wrench width:	60 mm
Hexagon angular dimension:	66.7 mm
Suitable for cable diameter:	30 ... 38 mm
Material:	Plastic
Material quality:	Polyamide (PA)
Surface protection:	Untreated
Halogen free:	Yes
Degree of protection (IP):	IP68
Shock resistant:	Yes
Colour:	Light grey
RAL-number:	7035
Model:	Straight
Type of sealing:	Sealing ring
Operating temperature:	-40 ... 100 °C (static)