

## MOSA M12 MALE 0° FIELD-WIREABLE (IDC)

B-cod., 3-pol., 0,25-0,34mm<sup>2</sup>, shielded

M12

Male straight

Field-wireable (IDC terminals)

B-coded, 3-pole, shielded

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Technical Data

Operating voltage	max. 32 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.25...0.34 mm <sup>2</sup> (AWG 22...24)
Sealing range (cable diameter)	7.0...8.8 mm
Outer wire diameter	2.0...2.6 mm
Protection	IP67 inserted and tightened (EN 60529)

#### General data

Temperature range	-25...+85 °C
-------------------	--------------

#### Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1