



Figure similar

TRANSFORMER SITAS; PHASES:1;  
 PN/PN(S6)(KVA):0,535 /2,35; UPRI(V):230+/-5%;  
 USEC(V):110; ISEC(A):4,82; F(HZ):50...60; VECTOR  
 GR./SHIELD WNG.:II0 /0; TA/ISOKL:40 /B; IP23; TYPE  
 OF TERMINALS:SCREW/TAB CONNECTION;  
 INSTALLATION:SCREW; EN 61558-2-1, -2-2, -2-4  
 >UL/CSA-RECOGNIZED< >CONTROL CIRCUIT  
 TRANSFORMER< >ISOLATION TRANSFORMER<

### General technical data:

Product designation		transformer SITAS
product brand name		SIDAC
Operating apparent output Rated value	V·A	535
Efficiency		0.92
Connection method for transformers		II0
Certificate of suitability		CE / cRUus
Product function		
• Temperature monitoring		No
• Insulation monitoring		No
• Short-circuit and overload proof		No
Number of shielding windings		0
Short-term vector power	V·A	2 350
Relative short-circuit voltage	%	3.7

### Inputs:

Phase number of the inputs		1
Input voltage		
• _1 Rated value	V	242
• _2 Rated value	V	230
• _3 Rated value	V	218
Electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60

### Outputs:

Phase number of the outputs		1
Output voltage		
<ul style="list-style-type: none"> <li>• _1 Rated value</li> </ul>	V	110
Electrical output frequency		
<ul style="list-style-type: none"> <li>• maximum</li> <li>• minimum</li> </ul>	Hz	60
	Hz	50

#### Ambient conditions:

Thermal class acc. to IEC 60085		B
Ambient temperature Rated value	°C	40
Protection class IP		IP23

#### Mechanical data:

Type of electrical connection		
<ul style="list-style-type: none"> <li>• at output for main current circuit</li> <li>• at input for main current circuit</li> </ul>		screw-type terminals / tab terminals screw-type terminals / tab terminals
Mounting type		screws
Construction form of the iron core		EI 150/48
Width	m	0.244
Height	m	0.245
Depth	m	0.23

#### Certificates/ approvals:

General Product Approval

Shipping Approval

other



[other](#)

#### Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM52424TJ100FC0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AM52424TJ100FC0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4AM52424TJ100FC0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM52424TJ100FC0&lang=en)

last modified:

15.01.2015