

LS01650/51

Attributes

- Plastic: ABS (basket; UL 94: HB); Mylar (diaphragm)
- Functionally at cold according to EN 60068-2-1/EN 50155
- weather-resistant
- UV-resistant

Technical Data

Rated power	2 W
Maximum power	3 W
Nominal impedance Z	8 & 50 Ohm
Frequency response	180–17000 Hz
Mean sound pressure level	84 dB (1 W/1 m)
Opening angle (-6 dB)	180°/4000 Hz
Excursion limit	+/-1 mm
Resonance frequency fs	300 Hz
Height of front pole-plate	2 mm
Voice coil diameter	10 mm
Height of winding	2.5 mm
Cutout diameter	46 mm
Net weight	0.048 g
Protective system	IP 65 *)
Temperature range	-40 ... 80 °C

