

## Datasheet



		A BELDEN B
Product description		
Description	panel-mounted socket for PCB	
Туре	MAB 7 SH-L	
Order No	930-518-500	
Type of contacts	female	
Number of contacts	7	
Standard	DIN EN 60 130-9; Pin assignment: DIN 41524	
Color housing	black	
Technical data		
Rated voltage	34V AC/DC	
Rated current *	4 A	
Pollution degree	3 acc. to DIN EN 60664-1 (VDE 0110-1)	
Type of connection	solder, PCB; THT-wave soldering	
Mating cycles	max. 50	
* Notice derating		
Materials		
Contact	CuZn	
Contact plating	Cu/Sn	
Contact bearer	PBT GF	
Environmental conditions		
Protection class (IEC 60529) *	IP30	
Temperature range	-20°C to +60°C, notice Derating	
* only if mounted and locked in combination with Hirs	schmann / Lumberg connector.	
Flammability class		
Contact bearer	UL 94 V-0	
Accessories		

Mating connectors / fitting to

cabel plug acc. to: DIN EN 60 130-9; Pin assignment: DIN 41524 (7 poles)

## Notes

Do not connect or disconnect under load.

