

Outdoor Pathlux Brick 3W 3000K 150lm IP65*Partcode: ILBLA017 / Page: 1*

Discover Integral's new outdoor range. Light up the exterior of your home with these compact, stylish and contemporary LED luminaires. Weatherproof and hard-wearing, this range is designed to last against the elements while bringing a designer look to your surroundings.

Gently illuminate your pathways with the stylish and hardwearing Pathlux. This model features a Brick design in dark grey.

[Watch Video](#)

Product Details

Partcode: ILBLA017

Check Code: 318387

Range Name: Outdoor

Product Type: Outdoor

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Optic: Clear Polycarbonate diffuser

Material: Polycarbonate body

Physical Data

Length: 210mm
Width: 85mm
Depth: 30mm
Weight (Unpackaged Single Unit): 226g
Luminaire Fixing: Wall Mounted


Electrical Data

Voltage Range: 220-240V
Power Consumption: 3.0 Watts
Driver included: Yes
Electric Current: AC
Frequency Range: 50/60 Hz
Power Factor: ≥ 0.30
Dimming: Non-dimmable
LVD Certified: Yes
EN: EN-60598

Light Data

Lumens: 150lm
Lumens per Watt: 50.0lm/W
Correlated Colour Temperature (CCT): 3,000k
Colour Temperature: Warm White
Colour Rendering Index (CRI): ≥ 80
LED Type: Surface mounted device (SMD)
Instant on - Less than 1 second: Yes
Lifetime: 25,000 hrs
Switching Cycles: $>12,500$ X

Environmental



Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 60 degrees

IP (Ingress Protection) Rating: IP65

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788232827

Length (unit of 1): 215mm

Width (unit of 1): 40mm

Depth (unit of 1): 100mm

Outer packaging info available on website

Product data last updated on: Thursday, October 25, 2018 - 16:17