


SDHK CONNECTOR



1.1 mm pitch/ Micro SD card Flip cover type



This is micro SD card cnnector of flip cover type that can approach from above the PC board surface.

Specifications

Current rating: 0.5 A AC/DCVoltage rating: 15 V AC/DC

• Temperature range: -25°C to +85°C

(including temperature rise in applying


electrical current)

Contact resistance: Initial value/ 80 mΩ max.

After environmental tests/ 160 mΩ max.

- Insulation resistance: 100 MΩ min.
- Withstanding voltage: 500 VAC/minute
- · Applicable card: Micro SD card
- * In using the products, refer to "Handling Precaution for Terminal and Connector" described on our website (Technical documents of Product information page).
- * Contact JST for details.
- * RoHS2 compliance

Connector



Model No.	Q'ty/reel
SDHK-8BNS-K-303-TB(HF)	1,400
Material and Finish	
Contact: Copper alloy, nickel-undercoated, gold-plated Housing: Heat resisting resin, black Cover: Stainless	

RoHS2 compliance

The product listed above are supplied on embossed-tape.

PC board layout

