

Product data sheet

Item No. 92.232.2063.1

Cable assembly GST18I3K1B- 15H 20SW

geis® Connection cable female - free end; length: 2m; type GST18I3; 3-pole; 250 V / 16 A; colour of coding: black with black strain-relief; cable: H05Z1Z1-F 3G1,5, colour: black



Item No.	92.232.2063.1
EAN	4015573412439
Order Unit	50 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	
Color of housing inclusive strain relief	Black

Model

Number of poles	3
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	37 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	S05Z1Z1-F



Cable colour	Black
Cable diameter	8 mm
Version of cable	Female - free end
Type of cord set	Connection cable
Version cable end 1	GST18i3 socket
Version cable end 2	Free end

Material

Surface finish	Tin-plated
Halogen free	Yes
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	2 m
--------------	-----

Technical drawing

.F	Farbe colour	Codierung *X*	Buchse female	Kabelfarbe cable colour
.1	schwarz black	N		schwarz black
.2	weiß white	L		weiß white
.3	grau grey	N L		schwarz black
.5	rot red	N L		schwarz black

Typ/type: GST1813K1B- 15H...
 SW = schwarz/black
 WS = weiß/white
 GR01 = grau/grey
 RT03 = rot/red

Teile-Nr. part-no.	L	Beispiel (Farbe: schwarz) example (colour: black)	Typ type
92.232.XX63.F	XX in dm-Schritten	92.232.1063.1 = 10dm/L= 1000mm	GST1813K1B- 15H 10SW
U2.232.XX63.F	XX in m-Schritten	U2.232.1263.1 = 12 m/L=12000mm	GST1813K1B- 15H X12SW
92.232.XX83.F	XX in dm-Schritten	92.232.1083.1 = 10dm/L= 1000mm	

83.F = spezielle Verpackung und Etikettierung nach A 1960.000
 special packaging and lable according to A 1960.000

Material: Weichblei/Soft lead
 Zulassung: 20.01. 01/07/01
 Zeichnung: 92.232.0263.1 01K b
 Made in mm@dimension are in mm

weitere Daten siehe Katalog
 further data see catalog