

Product data sheet

Item No. 92.238.1504.1

Cable assembly

geis® Connection cable male - free end; length: 1,5m; type GST18I3; 3-pole; 250 V / 20 A; colour of coding: black with black strain-relief; cable: H05VV-F 3G2,5, colour: black



Item No.	92.238.1504.1
EAN	4015573397385
Order Unit	40 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	
Color of housing inclusive strain relief	Black

Model

Number of poles	3
Nominal cross section conductor	2.5 mm ²
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	37 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	H05VV-F



Cable colour	Black
Cable diameter	10.2 mm
Version of cable	Male - free end
Type of cord set	Connection cable
Version cable end 1	GST18i3 plug
Version cable end 2	Free end

Material

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	1.5 m
--------------	-------

Technical drawing

.F	Farbe colour	Codierung *X* Stecker male	Kabelfarbe cable colour
.1	schwarz black	L R E N	schwarz black
.2	weiß white	L R E N	weiß white
.3	grau grey	L R E N	schwarz black
.5	rot red	L R E N	schwarz black

Teile-Nr. / part-no.
L
Beispiel (Farbe: schwarz) / example (colour: black)
Typ / type

92.238.XX04.F	XX in dm-Schritten	92.238.1004.1 = 10dm/L= 1000mm	GST1813K1-S 25 10SW
U2.238.XX04.F	XX in m-Schritten	U2.238.1204.1 = 12 m/L=12000mm	GST1813K1-S 25 X12SW

Typ/type: GST1813K1-S 25 ..
 SW = schwarz/black
 WS = weiß/white
 GR01 = grau/grey
 RT03 = rot/red

Kabel/cable H05VV-F3G2,5
 Farbe/colour: siehe Tabelle/see table

Weitere Daten siehe Katalog
 further data see catalog

PRE-ASSEMBLED CABLE
KONFERT LEITUNG
 Stecker/male-frees Ende/free and Crimpversion K1
 250V AC 20A 2,5mm