

UVC Germicidal T8

G55W T8
0002208



Product features

- Germicidal lamp for air and water purification.



PRODUCT OVERVIEW

Product name	G55W T8
Technology	Fluorescent
Lamp shape	Linear
Type	T8
Cap/Base	G13
General application	SPG
ETIM Class	EC002962
Light colour	UV
Wattage (W)	55
Average life (Nominal) (h)	8000
Product EAN number	5410288022086

DATA TABLE

General data

Product name	G55W T8
Technology	Fluorescent
Lamp shape	Linear
Type	T8
Cap/Base	G13
General application	SPG
ETIM Class	EC002962

Optical data

Light colour	UV
Adjustable chromaticity	N

Electrical data

Wattage (W)	55
Current (A)	0.77
Transformer required	Yes

UVC Germicidal T8 G55W T8 0002208

Lifetime data

Average life (Nominal) (h)	8000
----------------------------	------

Physical data

Max. Lamp Diameter (mm) - D	26
Weight (kg)	0.127

Packaging

Single packaging type	Carton
Product EAN number	5410288022086
Packaging single length / height (cm)	90.77
Packaging single width (cm)	2.8
Packaging single depth (cm)	2.8
DUN14 (inner)	25410288022080
Units per inner package	24
Packaging inner length / height (cm)	13.07
Packaging inner width (cm)	18.43
Packaging inner depth (cm)	93.1
DUN14 (outer)	15410288022083
Units per outer package	96
Packaging outer length / height (cm)	95.3
Packaging outer width (cm)	30.3
Packaging outer depth (cm)	39.6

Safety data

Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes
Intended purpose	Germicidal (UV-C)
Suitable for household illumination	No

TECHNICAL DRAWINGS

