

Heavy-duty workbench, series VS with 4.2 tonne load capacity

Solid beechwood 1500 mm, 3 drawers with full extension, 1 door



Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 80 x 80 x 3 mm, with brackets for screwing to the floor
- 3 drawers 100% full extension on the left, 3 x front height 180 mm, 1 door, height 540 mm on the right



Art. no.	50202 004
Brand	ANKE
Manufacturer Part Number	999.010.0004
Number of drawers	3 PCS
Working height	900 mm
Number of doors	1 PCS
Worktop width	1500 mm
Worktop height	100 mm
Pullout type	Full extension
Worktop depth	800 mm
Colour of front	Optional
Cabinet colour	Optional
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Levelling	No
Lock type	DOM® locking system
Drawer front height	3 x 180 mm
Surface	Powder-coated
Drawer width (inner dimension)	500 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Load-carrying capacity	4200 kg
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Material of worktop	Solid beech
Central locking	Yes
Gross Weight	196.000 kg
Product Group	502

EAN

4014641015268