

heavy-duty table, height-adjustable, max. dynamic load 2,000 kg

electrical height-adjustment from 710-1,080 mm

Execution:

- fully welded tubular steel frame with bolted stabilisation panels
- height-adjustable via 4 electric motors, coupled via electronic control unit, 370 mm stroke, controlled via keypad
- front sides with cover, incl. 10 x 10 mm square perforation, grid spacing 38 mm
- table top protrudes over base frame by 80 mm along each long side and by 62 mm along each short side
- square base plates, 140 x 140 mm, with perforation for ground anchoring
- tray shelves 640 mm deep, load capacity 100 kg
- multiplex beech worktop, 50 mm thick, oiled surface
- electrical connected load: 230 V/720 watts
- equipped with emergency stop switch and 3 CEE 7/4 sockets (front right)

Advantage:

- max. dynamic load 2,000 kg!
- table can be quickly and easily adjusted to the desired working height
- for perfect ergonomics in the workplace



Art. no.	50202 105
Frame colour	Selectable
Worktop width	2030 mm
Adjustable in height	Yes
Material of frame	Steel plate
Worktop height	50 mm
Max. height adjustment	1080 mm
Worktop depth	800 mm
Min. height adjustment	710 mm
Surface	Powder-coated
Dynamic load-carrying capacity	2000 kg
Material of worktop	Multiplex beech
Product Group	Prod. Gr. 5BC

EAN

4053625358984