

Electronics Super Knips ESD

Stainless steel polished, without chamfer, with or without wire clamp



Application:

For precision cutting tasks in electronics and precision mechanics fields.

Execution:

- INOX surgical stainless steel, air-hardened
- Polished head
- Ground, very sharp blades without chamfer for flush cutting
- Joint with stainless steel rivet
- With opening spring and opening limiter

Advantage:

- Safe, ergonomic and fatigue-free working thanks to two-component handles
- Precisely shaped tips also cut close-fitting wires from a diameter of 0.2 mm
- Extremely smooth action for fatigue-free working
- ESD design, discharges electricity



Art. no.	53107 090
Brand	KNIPEX
Manufacturer Part Number	78 03 125 ESD
Length	125 mm
Max. soft wire diameter cutting capacity	1.6 mm
Head design	Without bevel, Without wire clamp, Narrow
Surface	Plain
Material of handle	2-component plastic
ESD-capable	Yes
Gross Weight	0.057 kg
Product Group	535

EAN

4003773025146