


EG-Series EGT2 EG2/EN SCHALT.

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



The profiles of the switch and button components match those of the electronic components.
 Switches and buttons facilitate commissioning, servicing, monitoring and repair of industrial installations.

General ordering data

Type	EGT2 EG2/EN SCHALT.
Order No.	0104060000
Version	EG-Series, Relays, Rated control voltage: 250 V AC, Screw connection
GTIN (EAN)	4008190119713
Qty.	10 pc(s).

EG-Series EGT2 EG2/EN SCHALT.

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	58 mm	Width	18 mm
Height	50 mm	Net weight	42.6 g

Temperatures

Operating temperature	-25 °C...+85 °C	Ambient temperature	-25 °C...+85 °C
Storage temperature	-40 °C...+100 °C		

Rated data

Wire connection method	Screw connection
------------------------	------------------

Connection data

Clamping range, rated connection	6 mm ²	Clamping range, rated connection, min.	0.5 mm ²
Clamping range, rated connection, max.	6 mm ²	Wire connection cross section, finely stranded, max.	4 mm ²

Classifications

ETIM 3.0	EC001437	UNSPSC	30-21-19-17
eClass 5.1	27-37-16-01	eClass 6.2	27-37-16-01
eClass 7.1	27-37-16-01		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Declaration of Conformity	K011_07_09.pdf
---------------------------	--------------------------------