



634497

European Region

The Energizer® Hard Case Rechargeable Spotlight offers a wealth of power options. It uses 4 AA batteries and can charge NiMH batteries using the included wall adaptor or car charger. It stands up to rough treatment and provides an intense focused beam that illuminates objects up to 385 meters away.

VERSATILE

- Multiple power options – rechargeable AA NiMH, AA Lithium, AA Alkaline
- Recharge NiMH batteries with included car charger or wall adaptor



TOUGH

- Survives a 2-meter drop test
- Shatterproof lens



BRIGHT

- Provides 110 lumens
- Intense, focused beam



POWERFUL

- Illuminates objects up to 385 meters away
- Tight white spot is ideal for search applications




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

European Region Product Detail:

- Designation:** Energizer
Hard Case Rechargeable Spotlight
- SAP:** 634497
- Colour:** Black and Dark Grey
- Power Source:** Four "AA" Li, Alkaline or NiMH; on-board NiMH battery pack
- IEC:** LR6, FR6, 1.2H2
- Lamp:** High Output White LED
- Lamp Life (hr):** Lifetime
- Lamp Output (lumens):** 110
- Beam Distance (m):** 385
- Peak Beam Intensity (cd):** 37 000
- Run Time (h:mm):** 8:15 Li, 4:00 hrs NiMH, 2:30 Alk
- Typical Weight:** 7725 grams without replaceable batteries
- Dimensions (mm):** 230 x 108

Performance:



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved