

BZM27/Z0000/57/C Datasheet


Product Name // Horizontal Power Entry Module Mini

Bezel 57.5mm C14 Cold Condition Inlet (PX0575) 6.3mm Tab

Termination 2mm Panel Unfiltered Double Contact 4.8mm

Tab Switch Marked I/O

[View Product Page](#)



Panel Thickness 10, 15, 2.0, 3.0mm

BZM27/*****/xxx } A = 63.5 With Filter.
BZM28/*****/xxx } 29.1 Without Filter.

B = 54.9 With D.P. Switch. 45.9 With S.P. Switch.
C = 57.5 With D.P. Switch. 48.5 With S.P. Switch.

// Product Description:

- ⊕ Horizontal Power Entry Module Mini Bezel 57.5mm/48.5mm
- ⊕ C14 Cold Condition Inlet (PX0575)
- ⊕ Choice of Termination depending on part code:
- ⊕ Part codes prefixed BZM27: 6.3mm Tab
- ⊕ Part codes prefixed BZM42: 4.8mm Tab
- ⊕ Part codes prefixed BZM28: 2.8mm Tab
- ⊕ Choice of mains filter depending on part code:
- ⊕ Part codes containing /Z0000 are unfiltered
- ⊕ Choice of mains filter options (part codes containing codes starting /A)
- ⊕ Choice of other options as specified by individual part code, including switches with varying Terminations, indicators

// General Information:

Product Display Title:	Horizontal Power Entry Module Mini Bezel 57.5mm/48.5mm
Product Family:	IEC Connectors
Product Series:	Power Entry Modules
Current Max:	10A
Filter Type:	Unfiltered
Function:	C14 Inlets
iec Connector Components:	None
iec Connector Mates With:	PX0575
iec Filter Options:	Unfiltered
iec Horizontal Module Width:	57.5mm
Inlet Type:	C14 Cold Condition Inlet
Max Panel Thickness:	2mm
Min Panel Thickness:	2mm
Switch Type:	Double Contact 4.8mm Tab Marked I/O
Voltage Max:	250V

// Product PDF Links

[Power Entry Modules product data](#)