



Datenblatt - Fiche technique - Data sheet


11.04.5584



ROLINE HDMI High Speed Kabel mit Ethernet, HDMI BU - Micro HDMI ST,
0,15m

ROLINE Câble HDMI High Speed avec Ethernet, HDMI F - Micro HDMI M,
0,15m

ROLINE HDMI High Speed Cable + Ethernet, A - D, F/M, 0.15m



PIN ASSIGNMENT:

CONN.1	CONN.2	Signal Name
1	3	TMD5 Data2+
2	5	TMD5 Data2-
3	4	TMD5 Data2 Shield
4	6	TMD5 Data1+
5	8	TMD5 Data1-
6	7	TMD5 Data1 Shield
7	9	TMD5 Data0-
8	10	TMD5 Data0 Shield
9	12	TMD5 Clock-
10	14	TMD5 Clock+
11	13	TMD5 Clock Shield
12	15	CBC
13	2	UTILITY
14	1	HOT PLUG DETECT
15	16	DDA/CBC Ground
16	17	SCL
17	18	SDA
18	19	+5V Power
19	SHELL	SHELL

- NOTES:**
 1. RoHS & REACH COMPLIANT
 2. TESTING CONDITION:
 RATING TEMPERATURE: -10°C ~ +80°C
 RATING HUMIDITY: 10% ~ 55%
 RATING VOLTAGE: 30V.
 INSULATION RESISTANCE: DC/250V, 10MΩ MIN, 0.01S
 WITHSTAND VOLTAGE: AC/250V 5mA FOR 0.1S.
 CONDUCTOR RESISTANCE: 5Ω MAX.

rotronic

No.	TITLE	DESCRIPTION	Part Number	Note	***	3RD	8	9	10	11	12	13
5	PVC	OVER MOLDING : 40P BLACK										
4	PE	IN MOLDING : MG70 LDFE										
3	CONN	HDMI 19 PIN D/M TYPE, Shell Plated Ni + Contact GOLD FLASH	A/R									
2	CONN	HDMI 19 PIN A/F TYPE, Shell Plated Ni + Contact GOLD FLASH	1 PC									
1	CABLE	HDMI CABLE 1.4Rev With Ethernet 34AWG 70.06x5P+34AWG 70.06x4C PVC OD:4.8mm	1 PC									
ITEM NO. 11.04.5584												
DESC. ROLINE HDMI CABLE w/ETHERNET, AF-DM, 0.15M, BLACK												
SCALE NONE CHECK												
UNIT M/M APPROVED												
DATE 2013.07.18												
SHEET 1 OF 1												