

CUBE20S COUNTER MODULE

1X32Bit 2MHz


Counter module

1 × 32 Bit

max. 2 MHz

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Internal communication

Module Supply	24 V DC (20.4...28.8 V DC)
Current consumption	max. 70 mA

General data

Protection	IP20
Connection	Spring clamp plug-in terminals: max. 1.5 mm ² (AWG 16)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C (storage temperature -25...+70 °C)
Dimensions H × W × D	109×12.9×76.5 mm

Counter

Counter input	1
Counter frequency	max. 2 MHz
Counter depth	32 Bit (31 Bit + sign)

Diagnostic

Communication status	via LED
Diagnostic via LED	per module
Diagnostic via BUS	per module
Monitoring - under voltage	yes
Monitoring - no voltage	no
Short circuit and overload	yes

Commercial data

country of origin	TH
customs tariff number	90291000
minimum order quantity	1