



| Model | |
|---------------------|-------------|
| Product brand name | SENTRON |
| Product designation | accessories |





| Connections according IEC | |
|--|---------------------|
| Connectable conductor cross-section | |
| <ul style="list-style-type: none"> • for copper cable / finely stranded / minimum | 50 mm ² |
| <ul style="list-style-type: none"> • for copper cable / finely stranded / maximum | 240 mm ² |
| <ul style="list-style-type: none"> • for copper cable / stranded / minimum | 50 mm ² |
| <ul style="list-style-type: none"> • for copper cable / stranded / maximum | 300 mm ² |
| <ul style="list-style-type: none"> • for aluminum cable / stranded / minimum | 50 mm ² |
| <ul style="list-style-type: none"> • for aluminum cable / stranded / maximum | 300 mm ² |
| Wire stripping length | 28 mm |
| Tightening torque / when using copper cables | |
| <ul style="list-style-type: none"> • stranded | 42 |
| <ul style="list-style-type: none"> • finely stranded | 42 |

| Connections according UL | |
|-------------------------------------|--------|
| Wire stripping length | 1.1 in |
| Connectable conductor cross-section | |

- for copper cable / stranded / minimum 1 AWG
- for copper cable / stranded / maximum 600 kcmil
- for copper cable / finely stranded / minimum 1 AWG
- for copper cable / finely stranded / maximum 600 kcmil
- for aluminum cable / stranded / minimum 1 AWG
- for aluminum cable / stranded / maximum 600 kcmil

| | |
|--|-----------|
| Tightening torque / when using copper cables | |
| • stranded | 370 lb-in |
| • finely stranded | 370 lb-in |

Certificates

| General Product Approval | EMC | Declaration of Conformity | other |
|---|---|--|---|
|  UL |  |  RCM |  EG-Konf. |
| | | | Miscellaneous |

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9373-0JB13>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9373-0JB13>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9373-0JB13

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

08/28/2017