

SIVACON, base, IP30, D: 500 mm, W: 900 mm, galvanized



Figure similar

Model	
Product brand name	SIVACON
Design of the product	Closed
Design of the surface	galvanized
Design of the product / EMC version	No
Protection class IP	IP30
Product component	No
<ul style="list-style-type: none"> <li>• ventilation</li> </ul>	No
Mechanical Design	
Width	900 mm
Depth	500 mm
Net weight	5 000 g
Equipment marking	U
<ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> <li>• acc. to DIN EN 81346-2</li> </ul>	UC

EMC	Declaration of Conformity	Test Certificates	other
<a href="#">Miscellaneous</a>	 EG-Konf.	<a href="#">Special Test Certificate</a>	<a href="#">Miscellaneous</a>

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1095-2UB22-0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1095-2UB22-0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF1095-2UB22-0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1095-2UB22-0)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



