

## Profile Corner Surface 14

Profile Corner Surface 14 EF/T 2m anodised  
0022602



### Product features

- A 2000mm length anodised aluminium lighting profile that can be combined with slide (0022618) or click (0022619) opal diffusers with a maximum LED strip width of 14mm. Thanks to the angular design this profile offers two lighting angles (30° / 60°). This decorative profile design provides hidden mounting. Additional accessories like end caps, profile holders or mounting brackets need to be ordered separately.



## PRODUCT OVERVIEW

Product name	Profile Corner Surface 14 EF/T 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278027
Warranty	3 years
Housing colour	Silver
Product EAN number	5410288226026

## DATA TABLE

### General data

Product name	Profile Corner Surface 14 EF/T 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278027
Warranty	3 years

### Physical data

Housing colour	Silver
Nominal Product Length (mm)	2000
Nominal Product Width (mm)	24
Nominal Product Height (mm)	19.4
Weight (kg)	0.41

### Packaging

Single packaging type	Carton
Product EAN number	5410288226026
Packaging single length / height (cm)	200.0

## Profile Corner Surface 14

*Profile Corner Surface 14 EF/T 2m anodised*

0022602

Packaging single width (cm)	2.4
Packaging single depth (cm)	2.0
DUN14 (outer)	05410288226026
Units per outer package	50
Packaging outer length / height (cm)	205.0
Packaging outer width (cm)	16.0
Packaging outer depth (cm)	16.0

## TECHNICAL DRAWINGS

