

Clamping tool assortments

Basic assortment



Application:

For conventional clamping on machine tables with T-grooves, ideal for toolmaking.

Execution:

- All parts made of heat-treated steel
- Rolled thread
- T-slot screws heat-treated

Delivery:

Ref. no. 26152140: Clamp, 2 pcs. 14×100 mm, 2 pcs. 14×160 mm, clamping supports 4 pcs. Size 2, 4 pcs. Size 3, T-slot screws, 2 pcs. M14×16×63 mm; 4 pcs. M14×16×100 mm; 4 pcs. M14×16×160 mm stud bolts 2 pcs. Size M14×100, 2 pcs. Size M14×160, high nuts 6 pcs. Size M14, extension nuts 2 pcs. Size M14, washers 6 pcs. Size M14,



Art. no.	26152 160
Brand	AMF
Manufacturer Part Number	83915
Suitable for groove width	16 mm
Suitable for thread	M14
Tension force	28 kN
Clamping height	195 mm
Weight	11.1 kg
Gross Weight	11.027 kg
Product Group	260

EAN

4020772083915