

heavy-duty cabinet without centre divider – load capacity 1200 kg

with 4 shelves, width 1085 mm



Application:

For storing heavy materials, tools, stored goods, forming and stamping dies.

Execution:

- extremely robust and solid welded sheet steel construction with reinforced mounting profiles
- sheet steel shelves, galvanised, height-adjustable in 30 mm grid
- reinforced hinged doors, door opening angle 270°
- lockable with cylinder lock and rotary bolt lock with 3-point latching

Advantage:

- large storage space for bulky operational materials or heavy stored goods
- heavy parts are cleared and stored securely and conveniently
- extremely strong owing to high load capacity

Delivery:

fully assembled including floor anchoring



Art. no.	50147016
Brand	ANKE
Door design	Full-sheet panel
Width	1085 mm
Depth	630 mm
Height	1950 mm
Number of shelves	4
Load-carrying capacity per shelf	160 kg
Load-carrying capacity	1200 kg
With partition wall	No
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Gross Weight	143.579 kg
Product Group	502

EAN

4014641407902