

Cabinet workbench series L 1500 with lowerable transport unit

With 1 drawer with 80% partial extension and 1 door

Application:

The mobile workstation with versatile options for use.

Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- Door opening angle 180°

Advantage:

- Can be lifted, lowered and moved in all directions by simply moving the lever on the workbench
- In lowered state absolutely tilt-proof on four feet
- When you buy this product, you plant a tree and also receive a tree certificate!



Art. no.	50199 008
Brand	HK
Manufacturer Part Number	50199008
Number of fixed rollers	2 PCS
Working height	840 mm
Number of steering rollers	2 PCS
Worktop width	1500 mm
Number of drawers	1 PCS
Worktop height	40 mm
Number of doors	1 PCS
Worktop depth	750 mm
Pullout type	Partial extension
On castors	Yes
Moving device, can be lowered	Yes
Colour of front	Optional
Cabinet colour	Optional
With single pull-out safety brake	No
Surface	Powder-coated
With wheel lock	No
Load-carrying capacity	800 kg
Dynamic load-carrying capacity	400 kg
Wheel diameter	80 mm
Type	mobile/retractable
Lock type	Cylinder lock
Material of worktop	Multiplex beech
Drawer front height	1 x 180 mm
Material	Sheet steel
Drawer width (inner dimension)	490 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	490 x 598 mm
Drawer depth (inner dimension)	598 mm
Load-carrying capacity per drawer	70 kg
Material of wheel	PA - Polyamide
Central locking	Yes
Gross Weight	136.000 kg
Product Group	586

EAN

4053625083015