


Data Sheet

Type Number 329
Designation IEC ---
System Silver oxide / Zinc / Alkaline - Electrolyte



Nominal Voltage 1,55 V
Typical Capacity C 37 mAh
 Load 25,5 kOhm, at 20°C down to 1.2 V

Weight (approx.) 0,6 g
Volume 0,15 ccm
Coding..... Date of Manufacturing Month/Year

Temperature Ranges

	min	max.
Storage	0°C	60°C
Discharge	0°C	60°C

Dimensions

	min	max.
Diameter (Ø).....	7,75	7,9
Height (A/B)	2,85	3,1

Segment Watch

Main Applications Watch
 Photo
 Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	1.2 V
Continuous 24h/d,7d/w Current [µA]:	25500 Ω 61	Time:	600 h
		Capacity [mAh]:	37
		Energy [mWh]:	57