

Protect cover Han-INOX f hous. bulkhead



Part number	19 44 310 5421
Specification	Protect cover Han-INOX f hous. bulkhead
HARTING eCatalogue	https://b2b.harting.com/19443105421

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for cable to cable housing Metal

Version

Locking type	Single locking lever
Size	10 B
Field of application	Hoods/housings for harsh environments

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076



Pushing Performance

Specifications and approvals

CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	163.8 g
Country of origin	Germany
Customs tariff number	85389099
