


**Data sheet | Item number: 2104-5307**



3-conductor ground terminal block; with lever and push-button; 4 mm<sup>2</sup>; with test port; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 4,00 mm<sup>2</sup>; green-yellow



[www.wago.com/2104-5307](http://www.wago.com/2104-5307)



Color:



**Data**

**Connection data**

|                       |                     |
|-----------------------|---------------------|
| Connection technology | Push-in CAGE CLAMP® |
| Actuation type        | Push-in<br>Lever    |

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.



|                                                            |                                                                                                                                   |
|------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Connectable conductor materials                            | Copper<br>Copper                                                                                                                  |
| Nominal cross-section                                      | 4 mm <sup>2</sup>                                                                                                                 |
| Solid conductor                                            | 0.5 ... 6 mm <sup>2</sup> / 20 ... 10 AWG                                                                                         |
| Solid conductor; push-in termination                       | 1.5 ... 6 mm <sup>2</sup> / 14 ... 10 AWG                                                                                         |
| Fine-stranded conductor                                    | 0.5 ... 6 mm <sup>2</sup> / 20 ... 10 AWG                                                                                         |
| Fine-stranded conductor; with insulated ferrule            | 0.5 ... 4 mm <sup>2</sup> / 20 ... 12 AWG                                                                                         |
| Fine-stranded conductor; with ferrule; push-in termination | 1.5 ... 4 mm <sup>2</sup> / 18 ... 12 AWG                                                                                         |
| Note (conductor cross-section)                             | Depending on the conductor characteristic, a conductor with a smaller cross-section can also be inserted via push-in termination. |
| Strip length                                               | 11 ... 13 mm / 0.43 ... 0.51 inch                                                                                                 |
| Total number of connection points                          | 3                                                                                                                                 |
| Total number of potentials                                 | 1                                                                                                                                 |
| Number of levels                                           | 1                                                                                                                                 |
| Wiring type                                                | Front-entry wiring                                                                                                                |
| Number of jumper slots                                     | 2                                                                                                                                 |

### Physical data

|                                   |                      |
|-----------------------------------|----------------------|
| Width                             | 6.2 mm / 0.244 inch  |
| Height                            | 83.2 mm / 3.276 inch |
| Depth from upper edge of DIN-rail | 32.9 mm / 1.295 inch |

### Mechanical data

|               |                     |
|---------------|---------------------|
| Design        | horizontal type     |
| Mounting type | DIN-35 rail         |
| Marking level | Center/side marking |

### Material data

|                     |                  |
|---------------------|------------------|
| Color               | green-yellow     |
| Insulation material | Polyamide (PA66) |
| Weight              | 17.8 g           |

### Commercial data

|                       |               |
|-----------------------|---------------|
| Packaging type        | BOX           |
| Country of origin     | PL            |
| GTIN                  | 4055143992565 |
| Customs tariff number | 85369010000   |


Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
 Hansastr. 27  
 32423 Minden  
 Phone: +49571 887-0 | Fax: +49571 887-169  
 Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)




Do you have any questions about our products?  
 We are always happy to take your call at +49 (571) 887-44222.

## Approvals / Certificates


### Ex-Approvals

| Logo                                                                             | Approval           | Additional Approval Text | Certificate name |
|----------------------------------------------------------------------------------|--------------------|--------------------------|------------------|
|  | CCCEx<br>CQST/CNEx | CNCA-C23-01              | 2020312313000276 |

### Country specific Approvals



| Logo                                                                              | Approval                              | Additional Approval Text | Certificate name |
|-----------------------------------------------------------------------------------|---------------------------------------|--------------------------|------------------|
|   | CCA<br>DEKRA Certification B.V.       | EN 60947                 | NTR NL<br>7835   |
|   | CSA<br>DEKRA Certification B.V.       | C22.2                    | 80058036         |
|  | KEMA/KEUR<br>DEKRA Certification B.V. | EN 60947                 | 71-<br>114078    |

### UL-Approvals

| Logo                                                                               | Approval                             | Additional Approval Text | Certificate name |
|------------------------------------------------------------------------------------|--------------------------------------|--------------------------|------------------|
|  | UL<br>Underwriters Laboratories Inc. | UL 1059                  | E45172           |

## Required accessories

### End plate

|                                                                                   |                                                                                                        |                                                                    |
|-----------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------|
|  | Item no.: 2104-1391<br>End and intermediate plate; 1 mm thick; for 3-conductor terminal blocks; gray   | <a href="http://www.wago.com/2104-1391">www.wago.com/2104-1391</a> |
|  | Item no.: 2104-1392<br>End and intermediate plate; 1 mm thick; for 3-conductor terminal blocks; orange | <a href="http://www.wago.com/2104-1392">www.wago.com/2104-1392</a> |

Subject to changes. Please also observe the further product documentation!















## Compatible products














### Marking accessories

|                              |                                                                                                              |                                                                                  |
|------------------------------|--------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|
| * Item no.: 2009-110         | Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white                      | <a href="http://www.wago.com/2009-110">www.wago.com/2009-110</a>                 |
| * Item no.: 2009-115         | WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white       | <a href="http://www.wago.com/2009-115">www.wago.com/2009-115</a>                 |
| * Item no.: 2009-115/000-002 | WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow      | <a href="http://www.wago.com/2009-115/000-002">www.wago.com/2009-115/000-002</a> |
| * Item no.: 2009-115/000-005 | WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red         | <a href="http://www.wago.com/2009-115/000-005">www.wago.com/2009-115/000-005</a> |
| * Item no.: 2009-115/000-006 | WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue        | <a href="http://www.wago.com/2009-115/000-006">www.wago.com/2009-115/000-006</a> |
| * Item no.: 2009-115/000-007 | WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray        | <a href="http://www.wago.com/2009-115/000-007">www.wago.com/2009-115/000-007</a> |
| * Item no.: 2009-115/000-012 | WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange      | <a href="http://www.wago.com/2009-115/000-012">www.wago.com/2009-115/000-012</a> |
| * Item no.: 2009-115/000-017 | WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; light green | <a href="http://www.wago.com/2009-115/000-017">www.wago.com/2009-115/000-017</a> |
| * Item no.: 2009-115/000-023 | WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green       | <a href="http://www.wago.com/2009-115/000-023">www.wago.com/2009-115/000-023</a> |
| * Item no.: 2009-115/000-024 | WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet      | <a href="http://www.wago.com/2009-115/000-024">www.wago.com/2009-115/000-024</a> |
| ✓ Item no.: 2009-145         | Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white  | <a href="http://www.wago.com/2009-145">www.wago.com/2009-145</a>                 |
| ✓ Item no.: 2009-145/000-002 | Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow | <a href="http://www.wago.com/2009-145/000-002">www.wago.com/2009-145/000-002</a> |
| ✓ Item no.: 2009-145/000-005 | Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red    | <a href="http://www.wago.com/2009-145/000-005">www.wago.com/2009-145/000-005</a> |

Subject to changes. Please also observe the further product documentation!






|                                                                                    |                                                                                                                                                   |                                                                                  |
|------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|
|     | <b>Item no.: 2009-145/000-006</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue   | <a href="http://www.wago.com/2009-145/000-006">www.wago.com/2009-145/000-006</a> |
|     | <b>Item no.: 2009-145/000-007</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray   | <a href="http://www.wago.com/2009-145/000-007">www.wago.com/2009-145/000-007</a> |
|     | <b>Item no.: 2009-145/000-012</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange | <a href="http://www.wago.com/2009-145/000-012">www.wago.com/2009-145/000-012</a> |
|     | <b>Item no.: 2009-145/000-023</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green  | <a href="http://www.wago.com/2009-145/000-023">www.wago.com/2009-145/000-023</a> |
|     | <b>Item no.: 2009-145/000-024</b><br>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet | <a href="http://www.wago.com/2009-145/000-024">www.wago.com/2009-145/000-024</a> |
|    | <b>Item no.: 2009-191</b><br>Group marker carrier                                                                                                 | <a href="http://www.wago.com/2009-191">www.wago.com/2009-191</a>                 |
|    | <b>Item no.: 2009-192</b><br>Group marker carrier                                                                                                 | <a href="http://www.wago.com/2009-192">www.wago.com/2009-192</a>                 |
|   | <b>Item no.: 2009-193</b><br>Group marker carrier                                                                                                 | <a href="http://www.wago.com/2009-193">www.wago.com/2009-193</a>                 |
|  | <b>Item no.: 2009-198</b><br>Adaptor; gray                                                                                                        | <a href="http://www.wago.com/2009-198">www.wago.com/2009-198</a>                 |
|   | <b>Item no.: 248-501</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white                                           | <a href="http://www.wago.com/248-501">www.wago.com/248-501</a>                   |
|   | <b>Item no.: 248-501/000-002</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; yellow                                  | <a href="http://www.wago.com/248-501/000-002">www.wago.com/248-501/000-002</a>   |
|   | <b>Item no.: 248-501/000-005</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; red                                     | <a href="http://www.wago.com/248-501/000-005">www.wago.com/248-501/000-005</a>   |
|   | <b>Item no.: 248-501/000-006</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; blue                                    | <a href="http://www.wago.com/248-501/000-006">www.wago.com/248-501/000-006</a>   |
|   | <b>Item no.: 248-501/000-007</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; gray                                    | <a href="http://www.wago.com/248-501/000-007">www.wago.com/248-501/000-007</a>   |
|   | <b>Item no.: 248-501/000-012</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; orange                                  | <a href="http://www.wago.com/248-501/000-012">www.wago.com/248-501/000-012</a>   |

Subject to changes. Please also observe the further product documentation!

















|                                                                                   |                                                                                                                                                  |                                                                                |
|-----------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|
|    | <b>Item no.: 248-501/000-017</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; light green                            | <a href="http://www.wago.com/248-501/000-017">www.wago.com/248-501/000-017</a> |
|    | <b>Item no.: 248-501/000-023</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; green                                  | <a href="http://www.wago.com/248-501/000-023">www.wago.com/248-501/000-023</a> |
|    | <b>Item no.: 248-501/000-024</b><br>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; violet                                 | <a href="http://www.wago.com/248-501/000-024">www.wago.com/248-501/000-024</a> |
|    | <b>Item no.: 793-501</b><br>WMB marking card; as card; not stretchable; plain; snap-on type; white                                               | <a href="http://www.wago.com/793-501">www.wago.com/793-501</a>                 |
|    | <b>Item no.: 793-501/000-002</b><br>WMB marking card; as card; not stretchable; plain; snap-on type; yellow                                      | <a href="http://www.wago.com/793-501/000-002">www.wago.com/793-501/000-002</a> |
|    | <b>Item no.: 793-501/000-005</b><br>WMB marking card; as card; not stretchable; plain; snap-on type; red                                         | <a href="http://www.wago.com/793-501/000-005">www.wago.com/793-501/000-005</a> |
|    | <b>Item no.: 793-501/000-006</b><br>WMB marking card; as card; not stretchable; plain; snap-on type; blue                                        | <a href="http://www.wago.com/793-501/000-006">www.wago.com/793-501/000-006</a> |
|  | <b>Item no.: 793-501/000-007</b><br>WMB marking card; as card; not stretchable; plain; snap-on type; gray                                        | <a href="http://www.wago.com/793-501/000-007">www.wago.com/793-501/000-007</a> |
|  | <b>Item no.: 793-501/000-012</b><br>WMB marking card; as card; not stretchable; plain; snap-on type; orange                                      | <a href="http://www.wago.com/793-501/000-012">www.wago.com/793-501/000-012</a> |
|  | <b>Item no.: 793-501/000-017</b><br>WMB marking card; as card; not stretchable; plain; snap-on type; light green                                 | <a href="http://www.wago.com/793-501/000-017">www.wago.com/793-501/000-017</a> |
|  | <b>Item no.: 793-501/000-023</b><br>WMB marking card; as card; not stretchable; plain; snap-on type; green                                       | <a href="http://www.wago.com/793-501/000-023">www.wago.com/793-501/000-023</a> |
|  | <b>Item no.: 793-501/000-024</b><br>WMB marking card; as card; not stretchable; plain; snap-on type; violet                                      | <a href="http://www.wago.com/793-501/000-024">www.wago.com/793-501/000-024</a> |
|  | <b>Item no.: 793-5501</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white | <a href="http://www.wago.com/793-5501">www.wago.com/793-5501</a>               |

**Item no.: 793-5501/000-002**

Subject to changes. Please also observe the further product documentation!


















|                                                                                   |                                                                                                                                                                |                                                                                  |
|-----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|
|    | WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; yellow                                           | <a href="http://www.wago.com/793-5501/000-002">www.wago.com/793-5501/000-002</a> |
|    | <b>Item no.: 793-5501/000-005</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; red         | <a href="http://www.wago.com/793-5501/000-005">www.wago.com/793-5501/000-005</a> |
|    | <b>Item no.: 793-5501/000-006</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; blue        | <a href="http://www.wago.com/793-5501/000-006">www.wago.com/793-5501/000-006</a> |
|    | <b>Item no.: 793-5501/000-007</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; gray        | <a href="http://www.wago.com/793-5501/000-007">www.wago.com/793-5501/000-007</a> |
|    | <b>Item no.: 793-5501/000-012</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; orange      | <a href="http://www.wago.com/793-5501/000-012">www.wago.com/793-5501/000-012</a> |
|    | <b>Item no.: 793-5501/000-014</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; brown       | <a href="http://www.wago.com/793-5501/000-014">www.wago.com/793-5501/000-014</a> |
|    | <b>Item no.: 793-5501/000-017</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; green       | <a href="http://www.wago.com/793-5501/000-017">www.wago.com/793-5501/000-017</a> |
|  | <b>Item no.: 793-5501/000-023</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; light green | <a href="http://www.wago.com/793-5501/000-023">www.wago.com/793-5501/000-023</a> |
|  | <b>Item no.: 793-5501/000-024</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; violet      | <a href="http://www.wago.com/793-5501/000-024">www.wago.com/793-5501/000-024</a> |
| <b>Insulation stop</b>                                                            |                                                                                                                                                                |                                                                                  |
|  | <b>Item no.: 2004-171</b><br>Insulation stop; 0.25 - 0.5 mm <sup>2</sup> ; 5 pieces/strip; light gray                                                          | <a href="http://www.wago.com/2004-171">www.wago.com/2004-171</a>                 |
|  | <b>Item no.: 2004-172</b><br>Insulation stop; 0.75 - 1 mm <sup>2</sup> ; 5 pieces/strip; dark gray                                                             | <a href="http://www.wago.com/2004-172">www.wago.com/2004-172</a>                 |
| <b>Carrier rail</b>                                                               |                                                                                                                                                                |                                                                                  |
|  | <b>Item no.: 210-112</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm; silver-colored           | <a href="http://www.wago.com/210-112">www.wago.com/210-112</a>                   |
|  | <b>Item no.: 210-113</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored                            | <a href="http://www.wago.com/210-113">www.wago.com/210-113</a>                   |
|  | <b>Item no.: 210-114</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored                             | <a href="http://www.wago.com/210-114">www.wago.com/210-114</a>                   |

Subject to changes. Please also observe the further product documentation!














|                                                                                    |                                                                                                                                                      |                                                                  |
|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------|
|     | <b>Item no.: 210-115</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18 mm; silver-colored | <a href="http://www.wago.com/210-115">www.wago.com/210-115</a>   |
|     | <b>Item no.: 210-118</b><br>Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored                 | <a href="http://www.wago.com/210-118">www.wago.com/210-118</a>   |
|     | <b>Item no.: 210-196</b><br>Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored               | <a href="http://www.wago.com/210-196">www.wago.com/210-196</a>   |
|     | <b>Item no.: 210-197</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715; silver-colored                     | <a href="http://www.wago.com/210-197">www.wago.com/210-197</a>   |
|     | <b>Item no.: 210-198</b><br>Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; copper-colored                | <a href="http://www.wago.com/210-198">www.wago.com/210-198</a>   |
|     | <b>Item no.: 210-504</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; galvanized; according to EN 60715; silver-colored        | <a href="http://www.wago.com/210-504">www.wago.com/210-504</a>   |
|     | <b>Item no.: 210-505</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; galvanized; according to EN 60715; silver-colored      | <a href="http://www.wago.com/210-505">www.wago.com/210-505</a>   |
|     | <b>Item no.: 210-506</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; galvanized; similar to EN 60715; silver-colored       | <a href="http://www.wago.com/210-506">www.wago.com/210-506</a>   |
|   | <b>Item no.: 210-508</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; galvanized; similar to EN 60715; silver-colored         | <a href="http://www.wago.com/210-508">www.wago.com/210-508</a>   |
| <b>tools</b>                                                                       |                                                                                                                                                      |                                                                  |
|  | <b>Item no.: 210-658</b><br>Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; angled; short; multicoloured                      | <a href="http://www.wago.com/210-658">www.wago.com/210-658</a>   |
|  | <b>Item no.: 210-720</b><br>Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured                                     | <a href="http://www.wago.com/210-720">www.wago.com/210-720</a>   |
| <b>check</b>                                                                       |                                                                                                                                                      |                                                                  |
|   | <b>Item no.: 2004-511</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 1-pole; 4,00 mm²; gray                                    | <a href="http://www.wago.com/2004-511">www.wago.com/2004-511</a> |
|   | <b>Item no.: 2004-549</b><br>Spacer module; modular; e.g., for bridging commoned terminal blocks; gray                                               | <a href="http://www.wago.com/2004-549">www.wago.com/2004-549</a> |
|   | <b>Item no.: 2004-552</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 2-pole; 4,00 mm²; gray                                    | <a href="http://www.wago.com/2004-552">www.wago.com/2004-552</a> |
|   | <b>Item no.: 2004-553</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 3-pole; 4,00 mm²; gray                                    | <a href="http://www.wago.com/2004-553">www.wago.com/2004-553</a> |
|   | <b>Item no.: 2004-554</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 4-pole; 4,00 mm²; gray                                    | <a href="http://www.wago.com/2004-554">www.wago.com/2004-554</a> |

Subject to changes. Please also observe the further product documentation!



|                                                                                    |                                                                                                                                             |                                                                                  |
|------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|
|    | <b>Item no.: 2004-555</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 5-pole; 4,00 mm <sup>2</sup> ; gray              | <a href="http://www.wago.com/2004-555">www.wago.com/2004-555</a>                 |
|     | <b>Item no.: 2009-174</b><br>Test plug adapter; for 4 mm Ø test plugs; for testing TOPJOB®S rail-mounted terminal blocks; gray              | <a href="http://www.wago.com/2009-174">www.wago.com/2009-174</a>                 |
|     | <b>Item no.: 2009-182</b><br>Testing tap; for max. 2.5 mm <sup>2</sup> ; tool-free connection for individual test wires 0.08 - 2.5 mm; gray | <a href="http://www.wago.com/2009-182">www.wago.com/2009-182</a>                 |
|     | <b>Item no.: 210-136</b><br>Test plug; 2 mm Ø; with 500 mm cable; red                                                                       | <a href="http://www.wago.com/210-136">www.wago.com/210-136</a>                   |
| <b>Jumper</b>                                                                      |                                                                                                                                             |                                                                                  |
|    | <b>Item no.: 2004-402</b><br>Jumper; 2-way; insulated; light gray                                                                           | <a href="http://www.wago.com/2004-402">www.wago.com/2004-402</a>                 |
|    | <b>Item no.: 2004-403</b><br>Jumper; 3-way; insulated; light gray                                                                           | <a href="http://www.wago.com/2004-403">www.wago.com/2004-403</a>                 |
|    | <b>Item no.: 2004-404</b><br>Jumper; 4-way; insulated; light gray                                                                           | <a href="http://www.wago.com/2004-404">www.wago.com/2004-404</a>                 |
|    | <b>Item no.: 2004-405</b><br>Jumper; 5-way; insulated; light gray                                                                           | <a href="http://www.wago.com/2004-405">www.wago.com/2004-405</a>                 |
|   | <b>Item no.: 2004-405/011-000</b><br>Star point jumper; 3-way; insulated; light gray                                                        | <a href="http://www.wago.com/2004-405/011-000">www.wago.com/2004-405/011-000</a> |
|  | <b>Item no.: 2004-406</b><br>Jumper; 6-way; insulated; light gray                                                                           | <a href="http://www.wago.com/2004-406">www.wago.com/2004-406</a>                 |
|   | <b>Item no.: 2004-406/020-000</b><br>Delta jumper; insulated; light gray                                                                    | <a href="http://www.wago.com/2004-406/020-000">www.wago.com/2004-406/020-000</a> |
|  | <b>Item no.: 2004-407</b><br>Jumper; 7-way; insulated; light gray                                                                           | <a href="http://www.wago.com/2004-407">www.wago.com/2004-407</a>                 |
|  | <b>Item no.: 2004-408</b><br>Jumper; 8-way; insulated; light gray                                                                           | <a href="http://www.wago.com/2004-408">www.wago.com/2004-408</a>                 |
|  | <b>Item no.: 2004-409</b><br>Jumper; 9-way; insulated; light gray                                                                           | <a href="http://www.wago.com/2004-409">www.wago.com/2004-409</a>                 |
|  | <b>Item no.: 2004-410</b><br>Jumper; 10-way; insulated; light gray                                                                          | <a href="http://www.wago.com/2004-410">www.wago.com/2004-410</a>                 |
|  | <b>Item no.: 2004-433</b><br>Jumper; from 1 to 3; insulated; light gray                                                                     | <a href="http://www.wago.com/2004-433">www.wago.com/2004-433</a>                 |
|  | <b>Item no.: 2004-434</b><br>Jumper; from 1 to 4; insulated; light gray                                                                     | <a href="http://www.wago.com/2004-434">www.wago.com/2004-434</a>                 |

Subject to changes. Please also observe the further product documentation!

|                                                                                    |                                                                                                                                                                                            |                                                                  |
|------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------|
|    | <b>Item no.: 2004-435</b><br>Jumper; from 1 to 5; insulated; light gray                                                                                                                    | <a href="http://www.wago.com/2004-435">www.wago.com/2004-435</a> |
|    | <b>Item no.: 2004-436</b><br>Jumper; from 1 to 6; insulated; light gray                                                                                                                    | <a href="http://www.wago.com/2004-436">www.wago.com/2004-436</a> |
|    | <b>Item no.: 2004-437</b><br>Jumper; from 1 to 7; insulated; light gray                                                                                                                    | <a href="http://www.wago.com/2004-437">www.wago.com/2004-437</a> |
|    | <b>Item no.: 2004-438</b><br>Jumper; from 1 to 8; insulated; light gray                                                                                                                    | <a href="http://www.wago.com/2004-438">www.wago.com/2004-438</a> |
|    | <b>Item no.: 2004-439</b><br>Jumper; from 1 to 9; insulated; light gray                                                                                                                    | <a href="http://www.wago.com/2004-439">www.wago.com/2004-439</a> |
|    | <b>Item no.: 2004-440</b><br>Jumper; from 1 to 10; insulated; light gray                                                                                                                   | <a href="http://www.wago.com/2004-440">www.wago.com/2004-440</a> |
|    | <b>Item no.: 210-103</b><br>Wire commoning chain; insulated; black                                                                                                                         | <a href="http://www.wago.com/210-103">www.wago.com/210-103</a>   |
|    | <b>Item no.: 210-123</b><br>Wire commoning chain; insulated; blue                                                                                                                          | <a href="http://www.wago.com/210-123">www.wago.com/210-123</a>   |
| <b>ferrule</b>                                                                     |                                                                                                                                                                                            |                                                                  |
|   | <b>Item no.: 216-262</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray | <a href="http://www.wago.com/216-262">www.wago.com/216-262</a>   |
|  | <b>Item no.: 216-263</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red     | <a href="http://www.wago.com/216-263">www.wago.com/216-263</a>   |
|  | <b>Item no.: 216-264</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black | <a href="http://www.wago.com/216-264">www.wago.com/216-264</a>   |
|  | <b>Item no.: 216-266</b><br>Ferrule; Sleeve for 2.5 mm <sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue  | <a href="http://www.wago.com/216-266">www.wago.com/216-266</a>   |
|  | <b>Item no.: 216-267</b><br>Ferrule; Sleeve for 4 mm <sup>2</sup> / AWG 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray    | <a href="http://www.wago.com/216-267">www.wago.com/216-267</a>   |

## Downloads

### Documentation

#### Additional Information

|                        |            |               |          |
|------------------------|------------|---------------|----------|
| Technical explanations | 3 Apr 2019 | pdf<br>2.2 MB | Download |
|------------------------|------------|---------------|----------|

## CAD/CAE-Data

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
 Hansastr. 27  
 32423 Minden  
 Phone: +49571 887-0 | Fax: +49571 887-169  
 Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
 We are always happy to take your call at +49 (571) 887-44222.

#### CAD data

2D/3D Models 2104-5307

[URL](#)

[Download](#)

#### CAE data

ZUKEN Portal 2104-5307

[URL](#)

[Download](#)

### Environmental Product Compliance

#### Compliance Search

Environmental Product Compliance 2104-5307


[URL](#)

[Download](#)

3-conductor ground terminal block; with lever and push-button; 4 mm<sup>2</sup>; with test port; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 4,00 mm<sup>2</sup>; green-yellow

### Installation Notes

#### Conductor termination



All conductor types at a glance

### Product family

#### TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.