


RoHS

THIS IS A RoHS COMPLIANT COMPONENT/PRODUCT.



NOTES:

ELECTRICAL:

- 1. VOLTAGE RATING : 125 VAC
- 2. CURRENT RATING : 1.5 AMP.
- 3. CONTACT RESISTANCE : 100 MILLIOHMS MAX.
- 4. INSULATION RESISTANCE : 1000 MEGOHMS MIN. @ 500 VDC.
- 5. DIELECTRIC STRENGTH : 750 VAC 60Hz, 1 MIN.
- 6. CONFORM TO ANSI/TIA/EIA-568 B.2-1

MECHANICAL:

- 1. HOUSING MATERIAL : PC UL94V-0
- 2. INSERT MATERIAL : PBT+30%GF. UL94V-0
- 3. PCB MATERIAL : FR-4 THICKNESS 1.6 mm
- 4. CONTACT MATERIAL : PHOSPHOR BRONZE STAMP PIN t=0.35 mm
- 5. IDC CONTACT MATERIAL : PHOSPHOR BRONZE t=0.50 mm WITH NICKEL PLATING

- 6. WIRE : #24~26 AWG

ENVIRONMENTAL:

- 1. STORAGE : -40°C TO +85°C.
- 2. OPERATION : 0°C TO 70°C.

CONFORMING TO TIA/EIA 568B

MATES WITH MODULAR PLUG CONFORMING TO TIA-1096-A.

△ X1		ADD NEW P/N	HENRY	061518'
△	006000	NEW DESIGN	HENRY	102017'
MARK	ECN-NO.	REVISION RECORD	DRAWN	DATE
		UNLESS OTHERWISE SPECIFIED TOLERANCE	SCALE	CHECKED
		Dimension Range Tolerance	1/1	
		X.X ±0.20 UNIT mm	APPROVED	
		X.XX ±0.15		
		X.XXX ±0.10 SIZE A3		
		ANGLE ±5°		
Material/Plated/Notes		NAME		
SEE NOTE		CAT6 KEYSTONE JACK. RED		
Tooling No.		PART NO. 3261-0018-10	REV. 1	
		DOC. NO.		