


E70588



AS-Interface power distributor

QUAD M12 AS-i/24V 4A



Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current load total	[A]	2
Additional voltage supply	[V]	24 DC
Outputs		
Electrical design		AS-i
Operating conditions		
Ambient temperature	[°C]	-25...75
Protection		IP 65
Mechanical data		
Weight	[g]	95.3
Materials		PA 6.6; socket: stainless steel (1.4404 / 316L); screws: stainless steel (1.4404 / 316L); nut: stainless steel (1.4404 / 316L); O-ring: NBR; flat cable seal: NBR
Remarks		
Pack quantity		1 pcs.

Electrical connection	
1	AS-i +
2	0V
3	AS-i -
4	+24V
5	functional earth

Connector: M12

