





LV HRC FUSE BASDE, 690V(1000V) SINGLE-POLE,
160A, SIZE 00 CLIP-TYPE TERMINAL, 6X70SQMM

Model		
product brand name		SENTRON
Design of the product		LV HRC fuse base
General technical data		
Number of poles		1
Size of fuse system / acc. to DIN EN 60269-1		Other
Usage category		Without
circuit-breaker / Design		3NH30
Electricity		
rated current I _n / IEC, DIN/VDE / at 40 Cel	A	147.2
Current / with AC / Rated value	A	160
Product details		
Product component / Swivel mechanism		No
Connections		
Tightening torque / with screw-type terminals / maximum	N·m	14
Type of electrical connection		with saddle-type terminal
• for main current circuit		Saddle-type terminal
Mechanical Design		
Height	mm	122
Depth	mm	60
Mounting type		fixed mounting
Mounting type / bus-mounting		No

General Product Approval	Declaration of Conformity	Test Certificates
 KEMA	 GOST	
	 EG-Konf.	Special Test Certificate
		Type Test Certificates/Test Report

Shipping Approval	other
 GL	Environmental Confirmations

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NH3032>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3NH3032/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NH3032

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015