


Slides DZ 7957, Width 19.1 mm, to 160 kg, Full Extension

Material:

Slide elements: Cold rolled steel, bright zinc-plated.
Ball retainers: Cold rolled steel, zinc-plated.
Balls: Hardened steel.


Telescopic precision ball bearing slides for applications in the industrial and electronics sector.

- Suitable for drawers up to 1000mm wide at high load.
- Fast Disconnect.
- Optional Clip-On Brackets (page 630).
- Very high service life up to 80,000 cycles.
- Temperature range: -20°C to +70°C.



Accuride

Ordering details: e.g.: Prod. No. 649 039 12, Slides DZ 7957



Product No. per Pair	Slide Length mm	Travel +/-3.2 mm	A mm	B mm	C mm	D mm	E mm	F mm	G mm	H mm	I mm	J mm	K mm	L mm	M mm	N mm	Load Rating per Pair kg	Weight per Pair kg
649 039 12	305	305	-	-	-	-	-	-	-	179,4	198,5	-	-	184,2	200,2	241,3	140	2,38
649 039 14	356	356	-	-	-	-	-	-	-	230,2	249,3	-	-	235,0	251,0	292,1	140	2,80
649 039 16	406	406	108	-	-	-	-	236,6	262,0	281,0	300,1	-	-	285,8	301,8	342,9	150	3,19
649 039 18	457	457	108	-	-	-	-	287,4	312,8	331,8	350,9	-	-	336,6	352,6	393,7	150	3,62
649 039 20	508	508	108	171,5	-	-	-	338,2	363,6	382,6	401,7	-	-	387,4	403,4	444,5	160	4,03
649 039 22	559	559	108	171,5	-	-	328,7	389,0	414,4	433,4	452,5	-	-	438,2	454,2	495,3	160	4,42
649 039 24	610	610	108	171,5	-	-	379,5	439,8	465,2	484,2	503,3	-	-	489,0	505,0	546,1	160	4,84
649 039 26	660	660	108	171,5	-	-	430,3	490,6	516,0	535,0	554,1	-	-	539,8	555,8	596,9	160	5,27
649 039 28	711	711	108	171,5	-	-	481,1	541,4	566,8	585,8	604,9	-	-	590,6	606,6	647,7	160	5,88
649 039 30	762	762	108	171,5	-	-	531,9	592,2	617,6	636,6	655,7	203,2	469,9	641,4	657,4	698,5	160	6,06
649 039 32	813	813	108	171,5	-	-	582,7	643,0	688,4	687,4	706,5	203,2	520,7	692,2	708,2	749,3	160	6,48
649 039 34	864	864	108	171,5	349,3	-	633,5	693,8	719,2	738,2	757,3	203,2	571,5	743,0	759,0	800,1	160	6,88
649 039 36	914	914	108	171,5	349,3	501,7	684,3	744,6	770,0	789,0	808,1	203,2	622,3	793,8	809,8	850,9	160	7,29

Note

Recommended mounts: M5/M6 screw.

Use all mounting positions to achieve the max. load rating.

Handed slide assembly: Levers for front disconnection move in same direction.

For bracket accessory kit see page 630. The fixings included will not fit the 7957 slide. We recommend M6 countersunk screws.

Selection Tool
on the Internet at www.maedler.de
in the section **MÄDLER®-Tools**