

Product information

48 31 J3

Precision Circlip Pliers

For internal circlips in bore holes

With overstretching limiter

DIN 5256 C



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- With overexpansion guard (adjustable using end stop)
- Adjustment using hexagonal screw
- Ideal for series production as excessive expansion of rings is effectively prevented
- Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- DIN 5256 C, straight tips
- With overstretching limiter for standardised assembly in accordance with DIN 472
- The adjustable stop screw prevents the rings from overstretching
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened



General

| | |
|-----------------|-------------------------------|
| Article No. | 48 31 J3 |
| EAN | 4003773073888 |
| Pliers | grey atramentized |
| Handles | with non-slip plastic coating |
| Weight | 266 g |
| Dimensions | 225 x 50 x 14 mm |
| Standard | DIN 5256 C |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|-----------------|---------------|
| Size of bore | Ø 40 – 100 mm |
| Tips (diameter) | Ø 2.3 mm |

technical change and errors excepted